



### MOUNTING HARDWARE TYP 2 PLACES

#### NOTES:

1. CONFORMS TO PERFORMANCE REQUIREMENTS OF MIL-DTL-12883.
2. MATERIALS:  
HOUSING: POLYETHERIMIDE, COLOR: BLUE GREEN.  
GROMMET - SILICONE RUBBER PER A-A-59588, 50±10 DUROMETER, COLOR: RED
3. SOCKET CONTACTS CONFORM TO PERFORMANCE REQUIREMENTS OF MIL-C-39029/92.
4. COMPLETE MOUNTING HARDWARE SUPPLIED.
5. OPERATING TEMPERATURE -70°C TO 125°C.
6. CONTACT INSTALLATION TOOLS:  
\* 12 CONTACT - CRIMP TOOL: M22520/1-01  
POSITIONER: M22520/1-02  
INSERTION/REMOVAL: M81969/14-04  
\* 16 CONTACT - CRIMP TOOL: M22520/1-01  
POSITIONER: M22520/1-02  
INSERTION/REMOVAL: M81969/14-03

RELAY SOCKET P/N		SUPPLIED CONTACTS				MARKING
MILITARY	APCD	SIZE	MIL P/N	APCD P/N	QTY	
M12883/55-01	RSE112034	CONTACTS NOT SUPPLIED				M12883/55-01 J 58982 XXXX RSE112035
	RSE112035	12/12	M39029/92-535	CNS128900	3	
		16/16	M39029/92-533	CNS126900	2	
M12883/55-02	RSE112036	12/16	M39029/92-536	CNS129900	3	M12883/55-02 J 58982 XXXX RSE112036
		16/16	M39029/92-533	CNS126900	2	
	RSE112039	CONTACTS NOT SUPPLIED				

DIMENSIONS  ANSI Y14.5M UNITS: INCHES Pro/E FILE		TOLERANCES  .XX ±0.01 .XXX ±0.005 ANGLES ±2.0°		PROJECTION  		Amphenol Pcd SPECIFICATION DRAWING ENGR M. DiGIACOMO 3/2/2010		TITLE  RELAY SOCKET (3) SIZE 12, (2) SIZE 16 M12883/55					
ORIGINAL 		THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF AMPHENOL PCD INC. BEVERLY, MA, USA				CHKD  3/4/10  APPD  3/4/10		SIZE B		DWG NO. RSE112034		REV A	
						CODE: 58982				SHEET 1 OF 1			



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[RSE112035](#) [RSE112036](#) [RSE112034-S](#) [RSE112035-S](#) [RSE112036-S](#) [RSE112039-S](#)