




RSE112044



RSE112044

REV	ECN	DESCRIPTION	APP'D
-----	-----	-------------	-------



SUPPLIED CONTACTS			
SIZE	MIL PART NO.	PCD PART NO.	QTY
#12	M39029/92-535	CNS128900	3
#16	M39029/92-533	CNS126900	2
#22	M39029/92-531	CNS115900	2

- NOTES:
- CONFORMS TO PERFORMANCE REQUIREMENTS OF MIL-PRF-12883.
 - MATERIALS:
HOUSING - POLYETHERIMIDE, COLOR: BLUE-GREEN
GROMMET - SILICONE RUBBER PER ZZ-R-765, 50±10 DUROMETER, COLOR: RED
 - SOCKET CONTACTS CONFORM TO PERFORMANCE REQUIREMENTS OF MIL-C-39029/92
 - COMPLETE MOUNTING HARDWARE SUPPLIED AS SHOWN.
 - OPERATING TEMPERATURE -70° C TO +125° C.
 - CONTACT INSTALLATION TOOLS:
#12 CONTACT #16 CONTACT #22 CONTACT
CRIMP TOOL: M22520/1-01 M22520/1-01 M22520/2-01
POSITIONER: M22520/1-02 M22520/1-02 M22520/2-06
INSERTION/REMOVAL: M81969/14-04 M81969/14-03 M81969/14-01

DIMENSIONS ANSI Y14.5M UNITS: INCHES ACAD FILE	TOLERANCES .XX ±.01 .XXX ±.005 ANGLES ±2°	PROJECTION 	REFERENCE SPECIFICATION M12883/55-03			TITLE RELAY SOCKET SIZE 12/16/22		
			DRWN A. PATRIE 6/5/96					
			ENGR					
ORIGINAL	THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF PCD, INC. PEABODY, MA, USA		APPD J. RUTKOWSKI 8/9/96		SIZE B	DWG NO. RSE112044		REV B
					CODE: 58982	SCALE: 2X	SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[RSE112044](#) [RSE112044-S](#)