






5		6		7		8	
REV.	ECON. NO.	DATE	SIGN.	DESCRIPTION			



4	Black	4
3	Blue	3
2	White	2
1	Brown	1
Conn.1	Wire Color	Conn.2

Conn.1&2
Pin Assignments
Front View



TITLE			M12B Conn		
T Cable Screw			MM Conn MM Pin		
SCALE		Free	SHEET		1 OF 1
REV.	A	SIZE	A4	QC Inspection Item	

UNI:mm		
A		



Part	Quantity	Description	Unit	Material	Notes
1	1	Base Plate	MM	Aluminum	
2	4	Support Screws	MM	Steel	
3	2	Connectors	MM	Plastic	
4	1	Pin	MM	Steel	

 $\pm 0.5 \text{ mm}$

Amphenol LTW

安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
DWG NO SB-040400-MMO-TSAXX	Kenneth James	2007/12/03
CHECKED BY	DATE	
Ricky Valerio	2007/12/04	
APPROVED BY	DATE	
Cloud	2008/01/04	
CUSTOMER	ALTW	

Note:

- * **②** Important Dimension.
- * Waterproof Rate: IP68
- * Housing: Black, Polyurethane
- * Shielded Nut: Zinc Alloy, Nickel Plated
- * Male Pin: Copper Alloy, Gold Plated
- * Wire Harness: UL1007 24AWG, 4Pcs
- * Cable: UL2464 22AWG*4C+Talc
- * Black, PVC Jacket UV Resistant OD=5.0mm
- * Cable Length Tolerance: 1M~10M±5%mm,
- * 11M~99±500mm.
- Cable Length(L):0.1~99meters
- ALTW
CONFIDENTIAL
2007.12.03
R&D DEPT.


Cable Length(L):01~99Meters

99:99Meters

XX:01~99Meter

01:01Meter

02:02Meters



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[SB-040400-MM0-TSA05](#) [SB-040400-MM0-TSA02](#) [SB-040400-MM0-TSA10](#) [SB-040400-MM0-TSA01](#)