










REV.	ECN NO.	DATE	SIGN	DESCRIPTION


1	2	3	4	5	6	7	8
				THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTM. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTM.			
							
							
							
							
							

UNIT:mm		TITLE	M12 D 4Pin M Conn. M Pin,Y Cable
TOLERANCE	±0.5mm	SCALE	Free
REV.	A	SIZE	A4
1	2	SHEET	1 OF 1
		REV.	@@ :inspection item
		3	
		4	
		5	
		6	
		7	
		8	

4	Black	Black
3	Blue	Blue
2	White	White
1	Brown	Brown
	A	B
Conn.	Wire Color	

Pin Out

Pin Assignments
Front View 前視圖



Cable Length(L):01~99Meters

99:99Meters

XX:01~99Meter
01:01Meter
02:02Meters

Note:

* @@ Important Dimension.

(@@ 為重點檢驗尺寸)

* Waterproof Rate:IP68

* Housing:Black,PU


* Pin: Phosphor Bronze,Gold Plated

* Nut: Zn Alloy,Nicked Plated

* Cable: NO HALOGEN 22AWG*4C+INSULATION

Black,PU Jacket UV Resistant,OD=4.8mm

* Cable Length Tolerance:1M~10M±5%mm,11M~99M±500mm.



ITEM NO	DRAWN BY	DATE
DWG NO	Hu Min	2006/10/26
CUSTOMER	CHECKED BY	DATE
SD-040000-M00-YSBXX	Tina	2006/11/29
ALTW	APPROVED BY	DATE
	Liu yang zhi	2006/11/30
		8 FMM0702-01-01A2

Amphenol LTM
安費諾亮泰企業股份有限公司

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[SD-040000-M00-YSB10](#) [SD-040000-M00-YSB01](#) [SD-040000-M00-YSB05](#) [SD-040000-M00-YSB02](#)