





REV.	ECON NO.	DATE	SIGN	DESCRIPTION



ALTW  
DCC. DEPT.  
CONFIDENTIAL  
2008.01.31  
ISSUED



Black	4	4
Blue	3	3
White	2	2
Brown	1	1
Wire Color	Conn.1	Conn.2
Pin Out		



Note:

- \* **QC** Important Dimension.
- \* Waterproof Rate: IP68
- \* Housing: Black, Polyurethane
- \* Screw Nut: Zinc Alloy, Nickel Plated
- \* Female Pin: Copper Alloy, Gold Plated
- \* Wire Harness: UL1007 24AWG
- \* Cable: Black, UL2464 22AWG\*4C+Talc  
PVC Jacket UV Resistant OD=5.0mm
- \* Cable Length Tolerance: 1M~10M±5%, 11M~99±500mm.

99:99Meters  
Cable Length(L):01~99Meters

UNIT:mm			
TITLE			
M12 Conn T Cable Screw			
FF Conn FF Pin			
SCALE		Free	SHEET 1 OF 1
REV. A	SIZE A4	QC :inspection Item	
TOLERANCE ±0.5 mm			
A			
Amphenol LTW			
安費諾亮泰企業股份有限公司			
ITEM NO		DRAWN BY	
DWG NO		Ferdinand Velarde	
SD-040400-FF0-TSAXX		CHECKED BY	
CUSTOMER		Robert Dabu	
ALTW		APPROVED BY	
		Cloud	
		DATE	
		2007/11/29	
		DATE	
		2007/12/06	
		DATE	
		2008/01/04	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[SD-040400-FF0-TSA02](#) [SD-040400-FF0-TSA10](#) [SD-040400-FF0-TSA01](#) [SD-040400-FF0-TSA05](#)