





REV.	EGN NO.	DATE	SGN	DESCRIPTION



Pin Assignments	Wire Color
5	Green
4	Black
3	Blue
2	White
1	Brown
A	
B	
Conn.	

Pin Out

Note:
 * **@@** Important Dimension.
 * **(@@)** 為重點檢驗尺寸)
 * Waterproof Rate: IP68
 * Housing: Black, PU
 * Pin: Phosphor Bronze, Gold Plated
 * Ring: Green, Viton
 * Nut: Zn Alloy, Nicked Plated
 * Cable: NO HALOGEN 22AWG*5C+T, Black, PU Jacket, UV Resistant, OD=5.0mm
 * Cable Length Tolerance: 1M~10M±5%, 11M~99M±500mm.

Cable Length(L): 01~99Meters
 99:99Meters

XX: 01~99Meter
 01: 01Meter
 02: 02Meters

UNIT: mm	
TOLERANCE	±0.5mm
TITLE	M12 D 5Pin F Conn. F Pin, Y Cable
SCALE	Free
REV.	A
SIZE	A4
SHEET	1
OF	1
@@	Inspection Item

Amphenol LTW
 安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
DWG NO	HU Min	2006/10/26
CUSTOMER	CHECKED BY	DATE
ALTW	Ting	2006/11/29
	APPROVED BY	DATE
	Liu yang zhi	2006/11/30

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[SD-050000-F00-YSB01](#) [SD-050000-F00-YSB02](#) [SD-050000-F00-YSB10](#) [SD-050000-F00-YSB05](#)