


8 7 6 5 4 3 2 1

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL INTERCONNECT PRODUCTS CORP. ANY REPRODUCTION OR DISCLOSURE TO THIRD PARTIES, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL INTERCONNECT PRODUCTS CORP. IS PROHIBITED.

A/PC P/N	DESCRIPTION	CUSTOMER P/N	POWER CONSUMPTION	ATTENUATION	EYE & JITTER TEST	EPROM REV
647080001	QSFP LOOPBACK W/MODEL	SF-100GLB1.5W-0DB	1.5W	0 dB	NO	C
647080002	QSFP LOOPBACK W/MODEL	SF-100GLB0W00-0DB	---	0 dB	NO	C
647080003	QSFP LOOPBACK W/MODEL	SF-100GLB2.5W-0DB	2.5W	0 dB	NO	C
647080004	QSFP LOOPBACK W/MODEL	SF-100GLB1.5W-3DB	1.5W	3 dB	YES	C
647080005	QSFP LOOPBACK W/MODEL	SF-100GLB2.5W-3DB	2.5W	3 dB	YES	C
647080006	QSFP LOOPBACK W/MODEL	SF-100GLB1.5W-5DB	1.5W	5 dB	YES	C
647080007	QSFP LOOPBACK W/MODEL	SF-100GLB2.5W-5DB	2.5W	5 dB	YES	C
647080008	QSFP LOOPBACK W/MODEL	SF-100GLB1.5W-6DB	1.5W	6 dB	YES	C
647080009	QSFP LOOPBACK W/MODEL	SF-100GLB2.5W-6DB	2.5W	6 dB	YES	C
647080010	QSFP LOOPBACK W/MODEL	SF-100GLB0W00-3DB	---	3 dB	YES	C
647080011	QSFP LOOPBACK W/MODEL	SF-100GLB0W00-5DB	---	5 dB	YES	C
647080012	QSFP LOOPBACK W/MODEL	SF-100GLB0W00-6DB	---	6 dB	YES	C
647080013	QSFP LOOPBACK W/MODEL	SF-100GLB3.5W-0DB	3.5W	0 dB	NO	C
647080014	QSFP LOOPBACK W/MODEL	SF-100GLB3.5W-3DB	3.5W	3 dB	YES	C
647080015	QSFP LOOPBACK W/MODEL	SF-100GLB3.5W-5DB	3.5W	5 dB	YES	C
647080016	QSFP LOOPBACK W/MODEL	SF-100GLB3.5W-6DB	3.5W	6 dB	YES	C

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	NEW RELEASE PER EO 306707	11/15	DEC
B	REVISED PER ECN 306741	11/15	DEC
C	REVISED PER ECN 306765	12/15	DEC



ATTENUATION

POWER CONSUMPTION

ACD P/N

AMPHENOL CABLES ON DEMAND
SF-100GLBXXXX-XXX
QSFP+ LOOPBACK, X dB, X.XW
WW/YY
WWW.CABLESONDEMAND.COM
866-223-2860

BAG LABEL DETAIL

- THIS DRAWING IS RESERVED FOR AMPHENOL ACD (NO CUSTOMER DRAWING).
- PERMANENTLY MARK LABEL WITH INDICATED TEXT.
- ALL MATERIALS USED IN THE MANUFACTURE OF THIS ASSEMBLY SHALL COMPLY WITH AMPHENOL REGULATED MATERIALS SPECIFICATION CS-1152.
- TEST COMPLETED ASSEMBLIES PER AMPHENOL CS-1089. TEST ASSEMBLIES AT 10.31 Gbps AS NOTED IN P/N TABLE.
- SIMILAR TO AMPHENOL SPEC 63051XXXX.
- PROGRAM EPROM PER CS-1154. EPROM SERIAL No. MUST MATCH LABEL SERIAL No.
- INSTALL DUST COVER (ITEM 9) OVER CONNECTOR. COMPLETED ASSY SHALL BE PACKAGED IN AN APPROPRIATELY SIZED ANTI-STATIC BAG. PERMANENTLY LABEL BAG PER BAG LABEL DETAIL.



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE:		EAR NO.		Amphenol Interconnect Products Corp. 20 Valley St. Endicott, NY, 13760	
DECIMALS .X ±.X .XX ±.01 .XXX ±.005	ANGLES ± .5 °	APPROVALS		DATE	
		DRAWN D.CASHIMERE		11/15	
		CHECKED			
		THIRD ANGLE PROJECTION		RESP ENG	
		MFG ENG		SIZE DWG. NO. C 64708XXXX	
CAD FILE: S:\SolidWorks\PE 5 DIGIT NO\64708				REV. C	
				SCALE 1:1	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>SF-100GLB0W00-0DB</u>	<u>SF-100GLB1.5W-0DB</u>	<u>SF-100GLB3.5W-0DB</u>	<u>SF-100GLB0W00-3DB</u>	<u>SF-100GLB3.5W-3DB</u>
<u>SF-100GLB0W00-5DB</u>	<u>SF-100GLB1.5W-5DB</u>	<u>SF-100GLB2.5W-5DB</u>	<u>SF-100GLB3.5W-5DB</u>	<u>SF-100GLB0W00-6DB</u>