



TABLE I - PART NUMBER SCHEME		
PART NO.	CONTACTS SUPPLIED	PART MARKING
SJS503170P	NONE	SJS503170P
SJS503171P	(3) M39029/58-360	






LINEAR SPACING
.100 ON $\phi .116$
REF


2X $\phi .125$
ACCEPTS 4-40
OR M3 HARDWARE



GROMMET MARKING
TEXT HEIGHT: .040
COLOR: CONTRASTING



RCOMMENDED PANEL CUTOUT
PANEL THICKNESS: .050-.100



- NOTES:
- MATERIALS:
HOUSING: POLYETHERIMIDE, COLOR GREEN
CONTACT RETAINER: STAINLESS STEEL
GROMMET: SILICONE RUBBER PER A-A-59588, COLOR RED
 - FINISH:
HOUSING: NICKEL, 200 MICROINCHES MINIMUM
OVER COPPER, 120 MICROINCHES MINIMUM
 - PARTS ACCEPTS PIN CONTACTS PER TABLE I.
 - PART MATES WITH SJS830210P/211P
 - EST. WEIGHT: 1.5 GRAMS
 - SUPPLIED WITH DUST CAP.

DIMENSIONS	TOLERANCES	PROJECTION	Amphenol Pcd SPECIFICATION DRAWING			TITLE OVAL FLANGE RECEPTACLE SHELL SIZE 5 SJS PEGASUS 3 POS SIZE 22		
ANSI Y14.5M UNITS: INCHES Pro/E FILE	.XX ±0.01 .XXX ±0.005 ANGLES ±2.0°		ENGR ANDREW.WANG Mar-11-16	CHKD <i>Willie</i> 3/13/17	APPD <i>M. D. Lin</i> 3/13/17	SIZE B	DWG NO. SJS503170P	REV -
ORIGINAL	THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF AMPHENOL PCD INC., BEVERLY, MA			CODE: 58982	SCALE: 4:1	SHEET 1 OF 1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[SJS503170p](#)