






SJS830210P_C		
PART NO.	CONTACTS SUPPLIED	PART MARKING
SJS830210P	NONE	SJS830210P
SJS830211P	(3) M39029/57-354	

REV	ECN	APP'D
-	7678	



NOTES:

- MATERIALS:  
HOUSING: POLYETHERIMIDE  
CONTACT RETAINER: STAINLESS STEEL  
GROMMET & FACE SEAL: SILICONE RUBBER PER A-A-59588  
COUPLING NUT: PA66  
EMI SPRING: BERYLLIUM COPPER
- HOUSING: NICKEL, 200 MICROINCHES MINIMUM  
OVER COPPER, 120 MICROINCHES MINIMUM  
EMI SPRING: NICKEL, 100 MICROINCHES MINIMUM
- PART ACCEPTS SOCKET CONTACTS PER M39029/57-354
- PART MATES WITH SJS830230P/231P
- EST. WEIGHT: 1.8 GRAMS
- SUPPLIED WITH DUST CAP.

DIMENSIONS		TOLERANCES	PROJECTION	Amphenol Pcd SPECIFICATION DRAWING			
ANSI Y14.5M		.XX $\pm 0.01$		ENGR	ANDREW.WANG July-02-15		
UNITS: INCHES		.XXX $\pm 0.005$		CHKD	1/26/16		
Pro/E FILE		ANGLES $\pm 2.0^\circ$		APPD	1/26/16		
ORIGINAL		THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF AMPHENOL PCD INC., BEVERLY, MA		SIZE B	DWG NO. SJS830210P_C	REV -	
				CODE: 58982	SCALE: 4:1	SHEET 1 OF 1	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[SJS830210P](#)