







REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPR
A1	-	RELEASED DRAWING	Nov-8-17	Rookie	Tommy
A2	-	ADD THE GS PART NUMBER	Jan-28-19	Blink	Tommy
A3	-	CHANGE HAND CRIMPER	Nov-8-19	Flan	Tommy



CONTACT ORIENTATION ON ROLL
NOTES : (UNLESS OTHERWISE SPECIFIED)

- MATERIAL:
 - CONTACT BODY: COPPER ALLOY.
 - OUTER SPRING: STAINLESS STEEL.
- SPECIFICATIONS:
 - CURRENT RATING: 5A MAX.
 - TERMINATION TYPE: CRIMPING.
 - WIRE RANGE: 30~28AWG.
 - WIRE INSULATION DIA(MAX): Ø1.8mm.
- RoHS COMPLIANT.
- ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.
- AVAILABLE TOOLS:
 - HAND CRIMPER: MF-X-3958 (A3)
 - CRIMP APPLICATOR: MF-X-3957.
 - EXTRACTION TOOL: QXRT20.

P/N	CONTACT PLATING(MATING AREA)
SP28W2T	TIN PLATING OVER NICKEL.
SP28W2N	NICKEL PLATING OVER COPPERIZE.
SP28W2F	GOLD FLASH PLATING OVER NICKEL.
SP28W2G5	5µ" GOLD PLATING OVER NICKEL.
SP28W2G10	10µ" GOLD PLATING OVER NICKEL.
SP28W2G15	15µ" GOLD PLATING OVER NICKEL.
SP28W2G30	30µ" GOLD PLATING OVER NICKEL.



QUANTITY	PART NUMBER	DESCRIPTION	ITEM
MATERIALS LIST			
UNLESS OTHERWISE SPECIFIED			
1) All dimensions are in millimeters.			
2) Tolerances are as follows:			
3) Note reference =			
MATERIAL SPECIFICATIONS			
PROCESS SPECIFICATIONS			
NEXT ASBY			
SIGNATURES			
DATE			
DRAWN: Rm			
CHECKED: Mm			
ENGINEER: Tommy			
APPROVE: Tommy			
CUSTOMER: Nov-8-19			
THE DRAWING IS SUBJECT TO THE			
SPECIFICATIONS AND PERFORMANCE DATA			
OF THE MATERIALS USED IN THE MANUFACTURE			
OR REPRODUCTION ARE LIMITED. ALL			
MANUFACTURING VARIATIONS			
ECO-MATE PIN CONTACT.			
STAMPED, 28-30AWG, SIZE 20			
SIZE TYPE			
B C-			
SCALE NONE			
SHEET 1 OF 1			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[SP28W2G10](#)