




REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LE3-9A0081~84	2009/10/13	Li Xiu Zhi	Change Screw Nut



① SS-080000-M00-YS000

② ~ ③ Cable

SS-080000-M00-YSBXX




8	Red	紅	Red	紅
7	Blue	藍	Blue	藍
6	Pink	粉	Pink	粉
5	Grey	灰	Grey	灰
4	Yellow	黃	Yellow	黃
3	Green	綠	Green	綠
2	Brown	棕	Brown	棕
1	White	白	White	白
A		B		
Conn.		Wire Color		

Cable Length(L):01~99Meters

XX:01~99Meter
01:01 Meter
02:02Meters
:
99:99Meters

Note:

- * Important Dimension.
- * Waterproof Rate:IP68
- * Housing:PU,Black
- * Male Pin:Copper Alloy,Gold Plated
- * Screw Nut:ZN-ZDC-3,Nicked Plated
- * Cable:24AWG*8C+P PU Jacket VW-1 Black ,OD=5.2
- * Cable Length Tolerance:01M:40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm



Pin Assignments
Front View 前視圖

Pin Out

UNIT:mm	TITLE	
TOLERANCE	8Pin Male Conn. Male Pin	
±0.5mm	SCALE	SHEET
	Free	1 OF 1
	REV.	@@ Inspection Item
	B	A4
1	2	3

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
SS-080000-M00-YSBXX	Li Xiu Zhi	2009/10/13
CUSTOMER	CHECKED BY	DATE
ALTW	Rita	2009/10/14
	APPROVED BY	DATE
	Lion	2009/10/15

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[SS-080000-M00-YSB10](#) [SS-080000-M00-YSB05](#) [SS-080000-M00-YSB02](#) [SS-080000-M00-YSB01](#)