




REV.	ECN NO.	DATE	SIGN	DESCRIPTION



Conn.2&3

Pin Assignments

Front View




Conn.1

Pin Assignments



Front View

UNIT:mm		TITLE	M12 Conn T Adaptor MFF Conn MFF Pin,8Pin
TOLERANCE	±0.5 mm	SCALE	F ree
REV.	A	SIZE	A4
		SHEET	1
		OF	1
		Inspection Item	



8	Orange	橘	8	8
7	Yellow	黄	7	7
6	Gray	灰	6	6
5	Red	紅	5	5
4	Green	綠	4	4
3	Blue	藍	3	3
2	White	白	2	2
1	Black	黑	1	1
Conn.1	Wire Color	Conn.2	Conn.3	

Pin Out



- Note:
- * Important Dimension.
 - * Waterproof Rate:IP68.
 - * In 1 meter water within 24 hours.
 - * Connector:Black,PU.
 - * O-Ring:Green,Viton.
 - * Screw Nut:Zinc Alloy,Nickel Plated.
 - * Pin:Copper Alloy,Gold Plated.
 - * Wire Harness:UL1061 26AWG

Amphenol LTM	ITEM NO	SS-080808-MFF-TS001	DRAWN BY	H.Z.C.	DATE	2010/05/28
安費諾亮泰企業股份有限公司	DWG NO	SS-080808-MFF-TS001	CHECKED BY	Dick	DATE	2010/05/28
	CUSTOMER	ALTM	APPROVED BY	Luke	DATE	2010/05/28

1	2	3	4	5	6	7	8
---	---	---	---	---	---	---	---

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[SS-080808-MFF-TS001](#)