


REVISIONS				
REV	ECO	DESCRIPTION	DATE	BY APPR
A1	-	RELEASED DRAWING	Nov-8-17	Rookie Tommy
A2	-	ADD THE GS PART NUMBER	Jan-28-19	Blink Tommy
A3	-	CHANGE HAND CRIMPER	Nov-8-19	Flan Tommy



CONTACT ORIENTATION ON ROLL

NOTES: (UNLESS OTHERWISE SPECIFIED)

1. MATERIAL:

1.1. CONTACT BODY: COPPER ALLOY.

1.2. OUTER SPRING: STAINLESS STEEL.
2. SPECIFICATIONS:

2.1 CURRENT RATING: 5A MAX.

2.2 TERMINATION TYPE: CRIMPING.

2.3 WIRE RANGE: 22~20AWG.



2.4 WIRE INSULATION DIA(MAX): Ø2.6mm.
3. RSHS COMPLANT.
4. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.
5. AVAILABLE TOOLS:

5.1 HAND CRIMPER: MFX-3958.


A3

5.2 CRIMP APPLICATOR: MFX-3957.

5.3 EXTRACTION TOOL: QXRT20.



SECTION A-A



SECTION B-B

P/N	CONTACT PLATING(MATING AREA)
SS20W2T	TIN PLATING OVER NICKEL.
SS20W2N	NICKEL PLATING OVER COPPERIZE.
SS20W2F	GOLD FLASH PLATING OVER NICKEL.
SS20W2G5	5µ" GOLD PLATING OVER NICKEL.
SS20W2G10	10µ" GOLD PLATING OVER NICKEL.
SS20W2G15	15µ" GOLD PLATING OVER NICKEL.
SS20W2G30	30µ" GOLD PLATING OVER NICKEL.

QUANTITY	PART NUMBER	DESCRIPTION	ITEM
MATERIALS LIST			

A2

UNLESS OTHERWISE SPECIFIED			
1) All dimensions are in millimeters.			
2) Tolerances are as follows:			
1 Pk. DEC 40-20			
3 Pk. DEC 20-08			
3) Note reference =			
MATERIAL SPECIFICATIONS			
PROCESS SPECIFICATIONS		CUSTOMER	
THE DRAWING IS SUBJECT TO THE		ECO-MATE SOCKET CONTACT,	
SPECIFICATIONS AND PERFORMANCE DATA		STAMPED, 20-22AWG, SIZE 20	
THE MANUFACTURING VARIATIONS		SCALE: NONE	
NEXT ASBY		SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[SS20W2G10](#)