





REVISIONS				
REV	ECO	DESCRIPTION	DATE	BY APPR
A1	-	RELEASED DRAWING	Nov-8-17	Rookie Tommy
A2	-	ADD THE G5 PART NUMBER	Jan-28-19	Blink Tommy
A3	-	CHANGE HAND CRIMPER	Nov-8-19	Flan Tommy



CONTACT ORIENTATION ON ROLL
NOTES: (UNLESS OTHERWISE SPECIFIED)

- MATERIAL:
 - CONTACT BODY: COPPER ALLOY.
 - OUTER SPRING: STAINLESS STEEL.
- SPECIFICATIONS:
 - CURRENT RATING: 5A MAX.
 - TERMINATION TYPE: CRIMPING.
 - WIRE RANGE: 26~24AWG.
 - WIRE INSULATION DIA(MAX): Ø2.2mm.
- ROHS COMPLIANT.
- ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.
- AVAILABLE TOOLS:
 - HAND CRIMPER: MFX-3958. A3
 - CRIMP APPLICATOR: MFX-3957.
 - EXTRACTION TOOL: QXRT20.

P/N	CONTACT PLATING(MATING AREA)
SS24W2T	TIN PLATING OVER NICKEL.
SS24W2N	NICKEL PLATING OVER COPPERIZE.
SS24W2F	GOLD FLASH PLATING OVER NICKEL.
SS24W2G5	5µ" GOLD PLATING OVER NICKEL.
SS24W2G10	10µ" GOLD PLATING OVER NICKEL.
SS24W2G15	15µ" GOLD PLATING OVER NICKEL.
SS24W2G30	30µ" GOLD PLATING OVER NICKEL.



QUANTITY	PART NUMBER	DESCRIPTION	ITEM
MATERIALS LIST			
UNLESS OTHERWISE SPECIFIED			
1) All dimensions are in millimeters.			
2) Tolerances are as follows:			
1 Pt. DEC 40.20			
2 Pt. DEC 40.20			
3 Pt. DEC 20.08			
3) Note reference =			
SIGNATURES		DATE	
DRAWN:		Nov-8-19	
CHECKED:		Nov-8-19	
ENGINEER:			
APPROVE:		Nov-8-19	
MATERIAL SPECIFICATIONS		CUSTOMER	
PROCESS SPECIFICATIONS		THE DRAWING IS SUPPLIED FOR INFORMATION ONLY. IT DOES NOT CONTAIN SPECIFICATIONS AND PERFORMANCE DATA. THE MANUFACTURING CORPORATION NO RIGHTS OF REPRODUCTION ARE GRANTED. ALL MANUFACTURING VARIATIONS	
NEXT ASBY		SCALE NONE	
ECO-MATE SOCKET CONTACT, STAMPED, 24-26AWG, SIZE 20		SHEET 1 OF 1	

Amphenol

Sine Systems - www.amphenol-sine.com
44724 Monley Drive
Clinton Township, MI 48038

SS24W2XX

REVISION A3

SS24W2XX

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[SS24W2G10](#)