






REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	C191496	2019-08-27	NianPing Yu	Add UL Label
C	C192063	2019-12-03	NianPing Yu	△CXL



ALTW
CONFIDENTIAL
2019-12-03
R&D DEPT.


RECOMMENDED P.C.B. LAYOUT
GENERAL TOLERANCE IS ± 0.05




Notes:

- *  Important Dimension To Check.
- * Housing: High temperature thermoplastic.
UL94V-0, color is Natural white.
- * Pickup Cap: High temperature thermoplastic.
UL94V-0, color is Natural white.
- * Terminal: Copper Alloy, Gold Plated on contact
area. Tin plated on solder tails.
- * Solder Peg: Copper Alloy, Tin plated over Nickel.

UNIT:mm				TITLE SSL-1.1 DC 4P JACK CONN, WITH POST,S/T,SMT TYPE			Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO SSL11-J4A00-000001		DRAWN BY NianPing Yu		DATE 2019-08-27				
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES +1°				SCALE 5:1		SIZE A4			SHEET 1 OF 2		DWG NO SSL11-J4A00-000001		CHECKED BY Fisher Wang		DATE 2019-08-27		
REV. C				INC-REV. A.3		(QC): Inspection item			CUSTOMER ALTW		APPROVED BY Max Yang		DATE 2019-08-27				



1. 400Pcs Per Reel
2. 8 Reel Per Carton (3200Pcs/Carton)
3. Reference Standard: EIA-481-D
4. Net Weight: 0.7Kg/Carton.
5. Gross Weight: 4.1Kg/Carton.



A	UNIT: mm				TITLE SSL-1.1 DC 4P JACK CONN, WITH POST, S/T, SMT TYPE			Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO SSL11-J4A00-000001		DRAWN BY NianPing Yu		DATE 2019-08-27	
	TOLERANCE				SCALE 5:1		SIZE A4			DWG NO SSL11-J4A00-000001		CHECKED BY Fisher Wang		DATE 2019-08-27	
	.X ±0.25				SHEET 2 OF 2		WC-REV. A.5		CUSTOMER ALTW		APPROVED BY Max Yang		DATE 2019-08-27		
	.XX ±0.1														
	.XXX ±0.05														
ANGLES ±1°															
1		2		3		4		5		6		7		8	
														W10814-03-西01A2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[SSL11-J4A00-000001](#)