







REV.	ECN NO.	DATE	SIGN	DESCRIPTION
C	LE313C0108	2013-12-16	Fisher	Change Plating and Package
D	CI91496	2019-08-29	NianPing Yu	Add UL Label
E	CI92063	2019-12-03	NianPing Yu	EXI



RECOMMENDED P.C.B. LAYOUT
GENERAL TOLERANCE IS ±0.05




Notes:

- * Important Dimension To Check.
- * Housing: High temperature thermoplastic. UL94V-0, color is Natural white.
- * Terminal: Copper Alloy, Gold Plated on contact area. Tin plated on solder tails.
- * Solder Peg: Copper Alloy, Tin plated over Nickel.

UNIT: mm		TITLE	
TOLERANCE		SSL-1.1 DC JACK CONNECTOR 4-POS. W/O POST, SMT TYPE	
.X	±0.25	SCALE	6:1
.XX	±0.1	SIZE	A4
.XXX	±0.05	SHEET	1 OF 2
ANGLES	±1°	REV.	E
		WC-REV.	C.3
		Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO.	SSL11-J4D00-000001	DRAWN BY	NianPing Yu	DATE	2019-08-29
DWG NO.	SSL11-J4D00-000001	CHECKED BY	Fisher Wang	DATE	2019-08-29
CUSTOMER	ALTW	APPROVED BY	Max Yang	DATE	2019-08-29



MATERIALS

- 1. Carrier Tape: Polystyren (PS)
 - 2. Cover Tape: Polystyren (PS)
 - 3. Reel: Polystyren (PS)
- QUANTITY
- 1. 1000Pcs Per Reel
 - 2. 8 Reel Per Carton (8000Pcs/Carton)
 - 3. Reference Standard: EIA-481-D
 - 4. Net Weight: 1.68Kg/Carton.
 - 5. Gross Weight: 5.8Kg/Carton.

UNIT:mm		TITLE		ITEM NO		DRAWN BY		DATE	
TOLERANCE		SSL-1.1 DC JACK CONNECTOR		SSL11-J4D00-000001		NianPing Yu		2019-08-29	
.X ±0.25		4-POS. W/O POST, SMT TYPE		DWG NO		Fisher Wang		DATE	
.XX ±0.1		SCALE 5:1		SSL11-J4D00-000001		APPROVED BY		2019-08-29	
.XXX ±0.05		SIZE A4		CUSTOMER		Max Yang		DATE	
ANGLES ±1°		REV. E		ALTW				2019-08-29	
		WC-REV. C.3							
		SHEET 2 OF 2							
		QC: Inspection item							

Amphenol LTW
安費諾亮泰企業股份有限公司

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[SSL11-J4D00-000001](#)