

Table 1:				REV.	ECN NO.	DATE	SIGN	DESCRIPTION
P/N.	connector	Cable	White Print	A	Initial Release	2017-05-16	Fisher Wang	Rev. 01 to A
SSL12-J2LJ0-0XXFXX	White	White	Without	B	C210960	2021-06-25	Carl Dong	△ x1
SSL12-J2LJ0-0XXHXX	Black	Black	With					

Pin 1

Pin 2

9.0

12.5

White Print
(see table 1)

① Connector
(Color see table 1)

② Cable

41.4

23.1

△ B

L (mm)

W

H

Pin 1

Pin 2

Conn.

2	Red 紅
1	Brown 棕
Conn	Wire Color
Pin Out	

SSL12-J2LJ0-0XX X XX

XX: 1M~99M

01: 1M

02: 2M

...

99: 99M

F: White

H: Black

18: 18AWG(W=5.3,H=3.4)

20: 20AWG(W=5.0,H=3.2)

Cable Length Tolerance:

01M: ±40mm

02M~06M: ±60mm

06M~10M: ±100mm

11M~30M: ±200mm

31M~99M: ±500mm

Notes:

* ① Important Dimension To Check.

* Current Rating:5A

* Voltage Rating:300V DC/AC

* Waterproof Rate:IP68(mating)

1M Depth Of Water In 24 Hours.

* Housing: Thermoplastic, UL94V-0,

color see table 1.

* Terminal:Copper Alloy, Gold Plated.

* Seals: Silicone, Gray.

* Cable:UL21996, Flat Cable, UV Resistance,

color see table 1.

* Temperature Range: -40~+105℃

UNIT:mm

±0.5

TITLE

SSL1.2 2P,JACK CONN+FLAT CABLE

SCALE

Free

SIZE

A4

SHEET

1

OF

1

REV.

B

WC-REV.

A.2

①:Inspection item

Amphenol LTW

安費諾亮泰企業股份有限公司

ITEM NO

DWG NO

CUSTOMER

ALTW

DRAWN BY

Fisher Wang

CHECKED BY

Victor Hung

APPROVED BY

Kevin Hu

DATE

2017-05-16

DATE

2017-05-16

DATE

2017-05-16

1

2

3

4

5

6

7

8

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[SSL12-J2LJ0-020H01](#) [SSL12-J2LJ0-020F01](#) [SSL12-J2LJ0-018F01](#) [SSL12-J2LJ0-018H01](#)