



THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Table 1:

P/N.	connector	Cable	White Print
SSL12-J4LJ0-0XXFXX	White	White	Without
SSL12-J4LJ0-0XXHXX	Black	Black	With

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A	Initial Release	2017-05-17	Fisher Wang	Rev. 01 to A
B	C210960	2021-06-25	Carl Dong	△Bx1



SSL12-J4LJ0-0XX X XX

XX: 1M~99M
01: 1M
02: 2M
:
99: 99M

F: White
H: Black

18: 18AWG(W=9.2,H=3.4)
20: 20AWG(W=8.5,H=3.2)

Cable Length Tolerance:

01M: ±40mm
02M~06M: ±60mm
06M~10M: ±100mm
11M~30M: ±200mm
31M~99M: ±500mm

Notes:

- * Ⓞ Important Dimension To Check.
- * Current Rating:5A
- * Voltage Rating:300V DC/AC
- * Waterproof Rate:IP68(mating)
1M Depth Of Water In 24 Hours.
- * Housing: Thermoplastic, UL94V-0,
color see table 1.
- * Terminal:Copper Alloy, Gold Plated.
- * Seals: Silicone, Gray.
- * Cable:UL21996, Flat Cable, UV Resistance,
color see table 1.
- * Temperature Range: -40~+105℃

4	Yellow 黃
3	Orange 橘
2	Red 紅
1	Brown 棕
Conn	Wire Color
Pin out	

UNIT:mm		TITLE
±0.5		SSL1.2 4P, JACK CONN+FLAT CABLE
SCALE	Free	SIZE A4
REV.	B	WC-REV. A.4
		SHEET 1 OF 1
		QC:Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
	Fisher Wang	2017-05-17
DWG NO	CHECKED BY	DATE
SSL12-J4LJ0-0XXXXX	Victor Hung	2017-05-17
CUSTOMER	APPROVED BY	DATE
ALTW	Kevin Hu	2017-05-17

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[SSL12-J4LJ0-020H01](#) [SSL12-J4LJ0-020F01](#) [SSL12-J4LJ0-018F01](#) [SSL12-J4LJ0-018H01](#)