




P/N.	connector	Cable	White Print
SSL12-P2LP0-MXXFFX	White	White	Without
SSL12-P2LP0-MXXHXX	Black	Black	With

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A	Initial Release	2017-05-16	Fisher Wang	Rev. 01 to A
B	C210960	2021-06-25	Carl Dong	 x1



2	Red 紅
1	Brown 棕
Conn	Wire Color
Pin Out	

SSL12-P2LP0-MXX X XX

```
-XX: 1M~99M
01: 1M
02: 2M
.
99: 99M
```

—F: White
H: Black

-18: 18AWG (W=5.3, H=3.4)
20: 20AWG (W=5.0, H=3.2)

Cable Length Tolerance:

01M:	±40mm
02M~06M:	±60mm
06M~10M:	±100mm
11M~30M:	±200mm
31M~99M:	±500mm

Notes:

- *  Important Dimension To Check.
- * Current Rating:5A
- * Voltage Rating:300V DC/AC
- * Waterproof Rate:IP68(mating)
IM Depth Of Water In 24 Hours.
- * Housing: Thermoplastic, UL94V-0,
color see table 1.
- * Terminal:Copper Alloy, Gold Plated.
- * Gasket:Silicone, Gray.
- * Seals: Silicone, Gray.
- * Cable:UL21996, Flat Cable, UV Resistance,
color see table 1.
- * Temperature Range: -40~+105℃

UNIT:mm			TITLE SSL1.2 2P,PLUG CONN+FLAT CABLE			Amphenol LTW 安費諾亮泰企業股份有限公司	ITEM NO		DRAWN BY Fisher Wang		DATE 2017-05-16			
±0.5			SCALE Free		SIZE A4		SHEET 1	OF 1	DWG NO SSL12-P2LP0-MXXXXX		CHECKED BY Victor Hung		DATE 2017-05-16	
			REV. B		WC-REV. A.7		QC: Inspection item		CUSTOMER ALTW		APPROVED BY Kevin Hu		DATE 2017-05-16	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[SSL12-P2LP0-M20F01](#) [SSL12-P2LP0-M20H01](#) [SSL12-P2LP0-M18F01](#) [SSL12-P2LP0-M18H01](#)