






Poles \ Tol.	Dim A&B
2-4p	± 0.20
5-8p	± 0.25
9-16p	± 0.35
17-23p	± 0.40
24-30p	± 0.50

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		YK-446 Series						
PART NO.		YK446xx0xx00G			DWG NO.	8YK0001-446		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance	
		Guoxue 2014.01.08	Guoxue 2014.01.08		UNIT: mm		X. ±0.50	
					SCALE: NONE		X.X ±0.30	
				SHEET: 01/01	REV: H		X.XX ±0.10	
							X° ±1°	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>YK4460203000G</u>	<u>YK4460303000G</u>	<u>YK4460403000G</u>	<u>YK4460503000G</u>	<u>YK4460603000G</u>	<u>YK4460703000G</u>
<u>YK4460803000G</u>	<u>YK4460903000G</u>	<u>YK4461003000G</u>	<u>YK4461103000G</u>	<u>YK4461203000G</u>	<u>YK4461303000G</u>
<u>YK4461403000G</u>	<u>YK4461503000G</u>	<u>YK4461603000G</u>	<u>YK4461703000G</u>	<u>YK4461803000G</u>	<u>YK4461903000G</u>
<u>YK4462003000G</u>	<u>YK4462103000G</u>	<u>YK4462203000G</u>	<u>YK4462303000G</u>	<u>YK4462403000G</u>	<u>YK4462503000G</u>
<u>YK4462603000G</u>	<u>YK4462703000G</u>	<u>YK4462803000G</u>	<u>YK4462903000G</u>	<u>YK4463003000G</u>	