


Copying of this document and giving it to others and the use or communication of the contents thereof, are forbidden without express authority. Offenders are liable to the payment of damages. All rights are reserved in the event of the grant of a patent or the registration of the utility model or design.

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwertung und Mitteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugestanden. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patenterteilung oder Gebrauchsmuster-Eintragung vorbehalten.



D	Number of contacts	Standard	3	4	5	5	6	7	7	8	12	14	
	Contact arrangement	IEC 61076-2-106	03-a	04-a	05-a	05-b	06-a	07-a	07-b	08-a	12-a	14-a	
	Contact arrangement	IEC 60130-9 ⁿ	yes		no	yes		no	yes		no		
	Rated voltage ²⁾	IEC 60664-1	300 V (100 V)		300 V (63 V)	100 V (32 V)	300 V (63 V)		100 V (32 V)		150 V (32 V)		
	Rated voltage	UL 1977	250V									60V	
	Rated impulse withstand voltage ²⁾	IEC 60664-1	1500 V (1500 V)			1200 V (800 V)	1500 V (1500 V)		1200 V (800 V)				
	Pollution degree ²⁾	IEC 60664-1	1 (2)										
	Installation category	IEC 60664-1	I										
	Insulation group	IEC 60664-1	II, 400 ≤ CTI < 600										
	C	Current rating	IEC 60512-5-2 UL 1977	10A/+40°C		7A/+40°C							3A/+40°C
Insulation resistance		IEC 60512-3-1	>10 ¹⁰ Ohm ³⁾										
Contact resistance		IEC 60512-2-1	<5mOhm										
Climatic category		IEC 60668-1	40 / 100 / 56										
Temperatur range		IEC 60668-1	-40°C...+100°C / -40°F...+212°F										
IP degree		IEC 60529	IP 40										
Insertion and withdrawal force		IEC 60512-13-2	25N	30N	35N	35N	50N	55N	55N	60N	50N	50N	
mechanical operation		IEC 60512-9-1	Silver ≥500 mating cycles / Gold ≥1000 mating cycles										
housing material			brass and / or zinc die cast, nickel plated or thermoplast										
dielectric material			thermoplastic										
B	contacts		silver or gold plated, please order contacts separately acc. to drawing M-N 02 015 00XX X (3-8pol) or M-N 02 010 0158 X (12-14pol)										
	termination technique		crimp										
	wire gauge		0,09-1,0mm ²			0,09-0,75 mm ²	0,09-1,0 mm ²	0,09-0,75mm ²			0,09-0,25mm ²		
	flamability		UL 94 V0										
	locking system		metal screw coupling; tightening torque 0,7 - 1,5 Nm										

¹⁾ Edition 2000-05
²⁾ values in brackets are according to DIN EN 61076-2-106
³⁾ under operating conditions >10⁸ Ohm

Do not connect or disconnect under load. Metal housing parts shall be securely incorporated to protected ground.

Remark for gold plated contacts:
In order to avoid brittle inter-metallic connections, gold plated terminals have to be tin-plated in the solder area.
All technical data have been measured in a laboratory environment and can be different during practical usage of the product. Any product information is for descriptive usage only and not legally binding; particularly the information does not constitute or provide any legal guaranties ("Beschaffenheitsgarantie" or "Haltbarkeitsgarantie").

	14 (14-a)	T 3651 055 U
	12 (12-a)	T 3636 055 U
	8 (08-a)	T 3505 055 U
	7 (07-b)	T 3485 055 U
	7 (07-a)	T 3476 055 U
	6 (6-a)	T 3401 055 U
	5 (05-b)	T 3357 055 U
	5 (05-a)	T 3361 055 U
	4 (04-a)	T 3301 055 U
	3 (03-a)	T 3261 055 U
	2 (Pin 1+3)	T 3201 055 U
Contact arrangement View on mating side	Number of contacts (Contact arrangement acc. DIN EN 61076-2-106)	contact plating
Part number		

Gewicht (errechnet) / Calc WT: 47,46 g				Zul. Abw./Tolerances: ISO 2768-c		Maßstab / Scale: 2:1;1:1		A3			
Prüfmaß / Testdimension						DIN / ISO 13715		CUSTOMER DRAWING			
Teileindex / Partindexnumber:											
Bagatelle change:											
				Gez.	15.06.2021	Female cable connector r/a cable diameter 4-6mm					
				Drawn	MCARLE						
				Status	Released						
				Gepr.	16.06.2021						
				Checked	MBERTSCH						
Amphenol Tuchel Industrial GmbH						M FA T 3XXX 055 U				Blatt/ Sheet 1	
01	202100006	15.06.2021	MCARL							1 Bl.	
Index	Änderung/Description	Datum/Date	Name			Ers. f. / Replacement for :					
				</							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[T 3301 055](#)