

REV	ECN	APP'D
-	6087	

NOTES:

1. MATERIALS:

HOUSING - POLYETHERIMIDE, COLOR: BLACK.

GROMMET - SILICONE ELASTOMER, COLOR: BLUE

RESISTOR - 1/8W, $\pm 1\%$,

R1: 200K Ω RNC55H2003FS


R2: 200K Ω RNC55H2003FS

R3: 100K Ω RNC55H1003FS

R4: 100K Ω RNC55H1003FS



R5: 100K Ω RNC55H1003FS


2. MODULE SUPPLIED WITH 10 PIN CONTACTS, M39029/1-101; AND 2 SEALING PLUGS, MS24788-20.



INDEXING
INDICATOR

CIRCUIT
DIAGRAM



<div>DIMENSIONS</div> <div>ANSI Y14.5M</div> <div>UNITS: INCHES</div> <div>Pro/E FILE</div>	<div>TOLERANCES</div> <div>.XX ±0.01</div> <div>.XXX ±0.005</div> <div>ANGLES ±1.0°</div>	<div>PROJECTION</div> <div></div>	<div>Amphenol Pcd</div> <div>SPECIFICATION DRAWING</div> <div>ENGR</div> <div>E. RABINOWITZ04/18/07</div> <div>CHKD</div> <div>APPD</div>	<div>TITLE</div> <div>ELECTRONIC MODULE</div> <div>SZ 20 RESISTOR</div> <div>2X 200K Ω 3X 100K Ω, 1/8W</div>	
	<div>THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF AMPHENOL PCD, BEVERLY, MA</div>		<div>SIZE</div> <div>A</div>	<div>DWG NO.</div> <div>TJE120939_C</div> <div>CODE: 58982</div> <div>SCALE: 2:1</div>	<div>REV</div> <div>-</div> <div>SHEET 1 OF 1</div>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[TJE120939](#)