




REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-7B0138	2007/11/15	Gao Ling	Modify Panel Thickness
C	LEN1640311	2016/04/14	Vicky	Update Logo




- Note:
- * $\varnothing$ Important Dimension
 - * Housing: ABS 94V-0, Black
 - * Nut: Nylon+GF, Black
 - * Gasket: EPDM, Black
 - * PCB: FR-4, T=1.6mm
 - * Hosing: Nylon, PH=2.50mm
 - * Terminal: Female Pin, Tin Plated
 - * Cable: IP*28#+2C*24#+AL+MY+D+B, OD=5.0mm
 - * Use with waterproof cap or dust cap For Panel Thickness Max: 2.8mm
 - * Use without waterproof cap or dust cap For Panel Thickness Max: 4.0mm




5	Drain	地線	Shield
4	Black	24AWG 黑	4
3	Green	28AWG 綠	3
2	White	28AWG 白	2
1	Red	24AWG 紅	1
Housing	Wire Color	Conn.	
Pin Out			

Twist

Recommended
Panel Cut-Out



Pin Assignments
Front View



UNIT:mm		TITLE		Amphenol LTW		ITEM NO	DRAWN BY	DATE
		USB With Harness		安費諾亮泰企業股份有限公司		UA-20PMFP-SC8003	Vicky	2016-04-14
		Panel Screw M Conn F Pin				DWG NO	CHECKED BY	DATE
						UA-20PMFP-SC8003	Rita	2016-04-14
						CUSTOMER	APPROVED BY	DATE
						ALTW	Lisa	2016-04-14

TOLERANCE	
.X	±0.25
.XX	±0.1
.XXX	±0.05
ANGLES	±1°

SCALE	1:1	SIZE	A4	SHEET	1	OF	1
REV.	C	WC-REV.	A.3	QC: Inspection item			

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[UA-20PMFP-SC8003](#)