


THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A	Initial Release	2009/04/15	Doreen	Change REV.01 to REV.A
B	LEN1270113-117	2012/07/16	Jason Jiang	Change Cable Color To Gray
C	LEN15C0339-343	2015/12/09	Ruru	Change Logo LTW To Amphenol





UMC-05BMMM-SL8000
Color: Black


UMC-05BMMM-SL8AXX

XX : 01~99Meters
01 : 01Meter
02 : 02Meters
.....
99 : 99Meters

Cable Length(L): 01~99Meters



Note:
* $\varnothing$ Important Dimension.
* Waterproof Rate: IP68
* Connector: PU, Black
* Male Pin: Copper Alloy, Gold Plated
* Cable: (24#*1P+A)+(22#*1P+A)+D+AL/My+Braid
PVC UV Cable, OD=7.1mm, Gray
* Cable Length Tolerance: 01M: ± 40 mm
02M~05M: ± 60 mm
06M~10M: ± 100 mm
11M~30M: ± 200 mm
31M~99M: ± 500 mm



Pin Assignments
Front View

5	Blue	藍(24AWG)
4	White	白(24AWG)
3	Black	黑(24AWG)
2	Red	紅(24AWG)
1	Drain	地線(24AWG)
Conn.	Wire Color	
Pin Out		

UNIT:mm	
TOLERANCE	± 0.5 mm

TITLE M12 Male Conn. Male Pin,			
SCALE 2:1	SIZE A4	SHEET 1 OF 1	
REV. C	WC-REV. A.1	$\varnothing$ Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Ruru	DATE 2015-12-09
DWG NO UMC-05BMMM-SL8AXX	CHECKED BY Rita	DATE 2015-12-09
CUSTOMER ALTW	APPROVED BY Lisa	DATE 2015-12-09

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[UMC-05BMMM-SL8A05](#) [UMC-05BMMM-SL8A10](#) [UMC-05BMMM-SL8A01](#) [UMC-05BMMM-SL8A02](#)