







		2		3		4		5		6		7		8	
				REV.		ECN NO.		DATE		SIGN		DESCRIPTION			
				A		Initial Release		2018/03/24		Ethan					



UNIT:mm				TITLE Metal M12*1.5 VENT				Amphenol LTW 安費諾亮泰企業股份有限公司				ITEM NO VENT-MSINMS-08001		DRAWN BY Ethan		DATE 2018-03-24	
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°		SCALE 2:1		SIZE A4		SHEET 1 OF 2						DWG NO VENT-MSINMS-08001		CHECKED BY Feng-li		DATE 2018-03-24	
		REV. A		WC-REV. A.6		QC:Inspection item						CUSTOMER ALTW		APPROVED BY Jerry		DATE 2018-03-24	

1

2

3

4

5






6

7

8

W10814-03-2001A2

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

1		2		3		4		5		6		7		8																																
F Screw Nut: Optional part No.: APTM-AMBPC012-001 鐵件螺母作為選配件		E  M12*1.5		D  Through-hole Recommended Panel Cut-Out 建議開孔尺寸		C  Threaded-hole Recommended Panel Cut-Out 建議開孔尺寸		B 		A <table><tr><td>UNIT:mm</td><td></td><td></td><td colspan="3">TITLE Metal M12*1.5 VENT</td><td colspan="2">Amphenol LTW 安費諾亮泰企業股份有限公司</td><td>ITEM NO VENT-MSINMS-08001</td><td>DRAWN BY Ethan</td><td>DATE 2018-03-24</td></tr><tr><td colspan="3">TOLERANCE</td><td>SCALE 2:1</td><td>SIZE A4</td><td>SHEET 2 OF 2</td><td colspan="2"></td><td>DWG NO VENT-MSINMS-08001</td><td>CHECKED BY Feng-li</td><td>DATE 2018-03-24</td></tr><tr><td colspan="3">.X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°</td><td>REV. A</td><td>WC-REV. A.6</td><td colspan="2">QC: Inspection item</td><td colspan="2">CUSTOMER ALTW</td><td>APPROVED BY Jerry</td><td>DATE 2018-03-24</td></tr></table>		UNIT:mm			TITLE Metal M12*1.5 VENT			Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO VENT-MSINMS-08001	DRAWN BY Ethan	DATE 2018-03-24	TOLERANCE			SCALE 2:1	SIZE A4	SHEET 2 OF 2			DWG NO VENT-MSINMS-08001	CHECKED BY Feng-li	DATE 2018-03-24	.X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°			REV. A	WC-REV. A.6	QC: Inspection item		CUSTOMER ALTW		APPROVED BY Jerry	DATE 2018-03-24	Note: *  Important Dimension. * Waterproof Rate: IP68(Immersion for 60 minutes at a depth of 2 meter), IP69K * Housing: SUS316L * Cap: SUS316L * Membrane: ePTFE, Oleophobic * O-Ring: Silicone, 94V-0 * Air Permeability: >1600ml/min @70mbar	
												UNIT:mm			TITLE Metal M12*1.5 VENT			Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO VENT-MSINMS-08001	DRAWN BY Ethan	DATE 2018-03-24																								
												TOLERANCE			SCALE 2:1	SIZE A4	SHEET 2 OF 2			DWG NO VENT-MSINMS-08001	CHECKED BY Feng-li	DATE 2018-03-24																								
												.X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°			REV. A	WC-REV. A.6	QC: Inspection item		CUSTOMER ALTW		APPROVED BY Jerry	DATE 2018-03-24																								
REV.		ECN NO.		DATE		SIGN		DESCRIPTION																																						
A		E		D		C		B		A		 Recommended installation orientation 建議安裝朝向		THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.																																

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[VENT-MS1NMS-O8001](#)