





1 2 3 4 5 6 7



N=Number of Poles
Dim.L=Nx10.0-2.5
Dim.P=(N-1)x10.0

Dim	2P-4P	5P-8P	9P-12P
Dim.L	±0.20	±0.30	±0.40
Dim.P	±0.20	±0.30	±0.40

P.C.B LAYOUT

SIGN	DATE	DESCRIPTION	APPROVER
△	11/01'05	Standard spec is changed.	Marivn
△	02/01'07	Soldering temperature is changed from 245°C to 250°C	Marivn
△	08/20'09	Operating temperature is changed from -30° 105°C to -40° 115°C	Kind
△	08/20'09	drawing code changed.	Kind
△	08/25'10	Dim 15.2 TO 19.0	Tason
△	03/29'10	The wire inlet is changed.	Tason

Material

- Item Terminal body: steel stamping clamp Zinc plating
- Item Terminal screw: Steel Zinc plating “-” slot type
- Item Solder pin: Brass,Tin plated
- Item Firm wire chunk: steel Zinc plating
- Item Terminal housing: Thermoplastic (UL94 V-0)
- Item Terminal cover: Thermoplastic (UL94 V-0)

△ Electrical cULus

- Voltage rating: 300VAC
- Current rating: 20A
- Wire range:
- Solid wire(AWG): 12-22
- Stranded wire(AWG): 12-22
- Torque(Lb-In): 2.4
- Screw: M2.5
- Wire strip length: 10-11mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval: cULus

TR xx 15 x 0 xxxx G

COLOR			
02 2Poles	0 Black (RAL9005)	0000: “@” Logo	RoHS
03 3Poles	2 Red (RAL3001/D)	000A: “ANYTEK” Logo	Pb<40,000ppm
... ..	3 Orange(RAL2011/P)	Any special item by customer request. please contact sales department.	
12 12Poles	4 Yellow(RAL1018/A)		
	5 Green(RAL6018/T)		
	6 Blue (RAL5015/A)		
	8 Grey(RAL7035/D)		
	C Green(RAL 6018/U)		

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		TR 10.0 Series Vertical (90D wire inlet)			
PART NO.	TRxx15x0xxxxG	DWG NO.	8TR0302 △		
APPROVED		CHECKED		DESIGNED	Tason 2011.03.29
		DRAWN	Kind 2009.08.20	CUST NO.	
				Tolerance	
				UNIT: mm	X. ±0.50
				SCALE: NONE	X.X ±0.30
					X.XX ±0.10
					X° ±1°



SHEET: 01/01

REV.: H

1 2 3 4 5 6 7

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[TR0215500000G](#) [TR0315500000G](#) [TR0415500000G](#) [TR0515500000G](#) [TR0615500000G](#) [TR0715500000G](#)
[TR0815500000G](#) [TR0915500000G](#) [TR1015500000G](#) [TR1115500000G](#) [TR1215500000G](#)