





POLE		2	3	4	5	6	7	8	9	10
Dim.E		44.0	59.0	74.0	89.0	104.0	119.0	134.0	149.0	164.0
Dim.L		54.4	69.4	84.4	99.4	114.4	129.4	144.4	159.4	174.4
Dim.P		15.0	30.0	45.0	60.0	75.0	90.0	105.0	120.0	135.0
Tol.		±0.20			±0.35			±0.50		

SIGN	DATE	DESCRIPTION	APPROVER
△			
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

- Item ㉓ Terminal housing: PBT (UL94V-0)
- Item ㉔ Male contact : Copper. Gold plated.
- Item ㉕ With flange nut: Steel. zinc plated.

- Voltage rating: 600 V
- Current rating: 115 A
- Withstanding Voltage: 2.2 KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec

- G: Pb<40000ppm
- 0000: "@ " Logo (Standard)
- 000A: "ANYTEK" Mark

Any special item by
customer request.
please contact sales
department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		KU 15.0mm Body Series (Vertical) with flange 2P-10P					
PART NO.		KUxxC1x0xxxxG		DWG NO.		8KU0004	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance	
		Runner 2011.04.25	Runner 2010.05.24			UNIT: mm	X. ±0.50
						SCALE: NONE	X.X ±0.30
				SHFFT: 01/01		RFV: R	X° ±1°

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[KU02C1500000G](#) [KU03C1500000G](#) [KU04C1500000G](#) [KU05C1500000G](#) [KU06C1500000G](#) [KU07C1500000G](#)
[KU08C1500000G](#) [KU09C1500000G](#) [KU10C1500000G](#)