

10132797-AA B C D E F LF

AA	POSITION
01	2X05
02	2X10
03	2X15
04	2X20
05	2X25
06	2X30
08	2X40

*NOTE 6


B	DESCRIPTION
1	PLUG 1
2	PLUG 2
3	PLUG 3
4	PLUG 4
5	PLUG 5
6	PLUG 6
7	PLUG 7
















D	POLARIZATION PEG	HOLD DOWN
0	YES	YES
1	NO	YES
2	YES	NO
3	NO	NO

E	PACKAGING
0	TAPE AND REEL WITHOUT CAP

F	CUSTOMER CODE
BLANK	STANDARD P/N
V	APPLY FOR SPECIAL CUSTOMER

C	PLATING: CONTACT AREA/SOLDER TAIL AREA
1	1~3u"Au ON CONTACT AREA OVER 50u" Ni Min GOLD FLASH ON SOLDER TAIL OVER 50u" Ni Min






10132797 SERIES (PLUG SERIES)				
COMBINATION OF MATED HEIGHT 3.0~4.5mm	Plug 1 	Plug 2 	Plug 3 	Plug 4 
Recep 1 				
COMBINATION OF MATED HEIGHT 5.0~6.0mm	Plug 5 	Plug 6 	Plug 7 	
Recep 2 				


NOTE:

- MATERIAL:
HOUSING: THERMOPLASTIC BLACK UL94V-0
TERMINAL: COPPER ALLOY
HOLD DOWN: COPPER ALLOY
- PLATING:
TERMINAL: 1~3u"Au ON CONTACT AREA OVER 50u" Ni Min
GOLD FLASH ON SOLDER TAIL OVER 50u" Ni Min
HOLD DOWN: 100u" Tin Min ON SOLDER TAIL OVER 50u" Ni Min
- SEE GS-12-1298 FOR PRODUCT SPEC.
- PACKAGING: TAPE AND REEL WITHOUT CAP.
- THIS PRODUCT MEETS THE EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- 80 PIN IS OPTIONAL FOR ONLY PLUG 1.


mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection 1101	product family Bergstak			
ltr	ecn no	dr	date	tolerances unless otherwise specified			title 0.5mm PITCH BTB CONNECTOR PLUG			
E	ELX-N-36246-1	BY	2020/03/10	angles	linear					
				0°±2'		mm	scale 1:1			
				dr	Y-Y Bao	2020/03/10				
				engr	Y-Y Bao	2020/03/10				
				chr	Li-Qing Lei	2020/03/10				
				appd	Tim Yao	2020/03/10				
sheet index	revision	E					dwg no 10132797			
	sheet	1/3								
							type Product Customer Drawing			



0.08
(ALL CONTACTS & HOLD DOWNS)



TYPE	"H"
PLUG 1	2.30
PLUG 2	2.80
PLUG 3	3.30
PLUG 4	3.80






RECOMMENDED PCB LAYOUT

pin.No.	A	B	C	D	E
10	4.70	2.00	4.70	4.10	5.50
20	7.20	4.50	7.20	6.60	8.00
30	9.70	7.00	9.70	9.10	10.50
40	12.20	9.50	12.20	11.60	13.00
50	14.70	12.00	14.70	14.10	15.50
60	17.20	14.50	17.20	16.60	18.00
80	22.20	19.50	22.20	21.60	23.00



PLUG 1~4

mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection 1101	product family Bergstak			
ltr	ecn no	dr	date	tolerances unless otherwise specified		mm	title 0.5mm PITCH BTB CONNECTOR PLUG			
E	-	BY	2020/03/10	angles	linear	mm	dwg no 10132797			
				0°±2'		scale 1:1	sheet 2 of 3			
				dr	Y-Y Bao	2020/03/10	size A3			
				engr	Y-Y Bao	2020/03/10	Amphenol FCI			
				chr	Li-Qing Lei	2020/03/10				
				appd	Tim Yao	2020/03/10	type Product Customer Drawing			
sheet index	revision	E								
	sheet	2/3								



0.08
(ALL CONTACTS & HOLD DOWNS)

TYPE	"H"
PLUG 5	4.30
PLUG 6	4.80
PLUG 7	5.30



pin.No.	A	B	C	D	E
10	4.70	2.00	4.70	4.10	5.50
20	7.20	4.50	7.20	6.60	8.00
30	9.70	7.00	9.70	9.10	10.50
40	12.20	9.50	12.20	11.60	13.00
50	14.70	12.00	14.70	14.10	15.50
60	17.20	14.50	17.20	16.60	18.00

PLUG 5~7

mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection 1101	product family Bergstak			
ltr	ecn no	dr	date	tolerances unless otherwise specified			title 0.5mm PITCH BTB CONNECTOR PLUG			
E	-	BY	2020/03/10	angles	linear	mm	dwg no 10132797			
				0°±2'		scale 1:1	sheet3 of 3 size A3			
				dr	Y-Y Bao	2020/03/10	type Product Customer Drawing			
				engr	Y-Y Bao	2020/03/10				
				chr	Li-Qing Lei	2020/03/10				
				appd	Tim Yao	2020/03/10				
sheet index	revision sheet	E 1/3								

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[10132797-081120LF](#)