



REV.	DATE	DESCRIPTION
NC	06/21/05	INITIAL RELEASE



- NOTE:
1. CRIMPED FERRULE
HEX CRIMP SIZE .255"
 2. CONTACT PIN TO SOLDER

Amphenol Connex

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES. UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS ARE FOR CUSTOMER REFERENCE ONLY.			APPROVALS		DATE		PART DESCRIPTION			
8			DRAWN	G.R.S.	06/21/05		TNC REVERSE POLARITY R/A CRIMP PLUG (FOR BELDEN RG-8/X, TIMES LMR-240)			
7			UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:		CHECKED		PART NO.			
6			0.5 - 8mm ± 0.20mm		ISSUED		122414RP			
5	COVER	BRASS	8 - 30mm ± 0.40mm		SHEET					
4	FERRULE	COPPER	30 - 120mm ± 0.50mm		1 OF 1					
3	CONTACT PIN	PHOS. BRONZE	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:							
2	INSULATOR	TEFLON	.020 - .315 = ± 0.007"							
1	BODY/SHELL	BRASS	.315 - 1.180 = ± 0.015"							
			1.180 - 4.724 = ± 0.020"							
	DESCRIPTION	MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING					
					CAD FILE					
					C:/122/122414RP.DWG					
					DWG. NO.		REV		SIZE	
					122414RP.DWG		NC		A	
									SCALE	
									NA	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[122414RP](#)