

NOTES:

1. MATERIALS AND FINISHES:
BODY-BRASS, NICKEL PLATING
REAR BODY & CONTACTS - BeCu, GOLD PLATING
COUPLING NUT - STAINLESS STEEL, GOLD PLATING

3. MECHANICAL:
A. DURABILITY: 500 CYCLES MIN.
B. TEMPERATURE RANGE: -65° C TO +165° C

THIRD ANGLE PROJ.

REV

DESCRIPTION

DATE

ECO

APPR

--

RELEASE TO MFG.

--

--

--


F

COD SHEET ADDED


6/1/15

50343

CL



SCALE 1.500



CUSTOMER OUTLINE DRAWING
ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES AND TOLERANCES ARE: 2 PLACE DECIMAL 3 PLACE DECIMAL ANGLES ±.015 (0.381 mm) ±.005 (0.127 mm) ± 1° NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.	MATERIAL SEE NOTES	DRAWN CLEMENT	DATE 13-Jan-15	TITLE SMA STR PLUG TO BNC JACK ADAPTER		Amphenol RF www.amphenolrf.com	
	REFERENCE EPA 802202-51 RCA NAVORD 2901128	ENGINEER O.BARTHELMES	DATE 21-Jun-06			DRAWING NO.901-166	
	CONFIGURATION LEVEL: In Work	APPROVED K. CAPOZZI	DATE 6/1/15	SCALE: 10.0:1.0 SHEET 2 OF 2		ITEM NO.901-166	
	FINISH	CAD FILE		DWG SIZE B		REV F	PART NO.901-166

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[901-166](#)