


REV.	DATE	DESCRIPTION
NC	06/08/99	INITIAL RELEASE
A	03/28/08	UPDATE DRAWING FORMAT



8				
7				
6				
5				
4				
3	CONTACT PIN	BER. COPPER	SILVER	1
2	INSULATOR	TEFLON	NATURAL	1
1	BODY	BRASS	NEXCOTE	1
	DESCRIPTION	MATERIAL	FINISH	QTY

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE  
IN MILLIMETERS. DIMENSIONS IN [ ] ARE IN  
INCHES AND FOR CUSTOMER REFERENCE ONLY.

UNLESS OTHERWISE SPECIFIED  
TOLERANCES FOR MILLIMETERS ARE:

0.5 – 8mm  $\pm$  0.20mm  
8 – 30mm  $\pm$  0.40mm  
30 – 120mm  $\pm$  0.50mm

UNLESS OTHERWISE SPECIFIED  
TOLERANCES FOR INCHES ARE:

.020 – .315 =  $\pm$  0.007"  
.315 – 1.180 =  $\pm$  0.015"  
1.180 – 4.724 =  $\pm$  0.020"

APPROVALS

DATE

DRAWN G.R.S.

03/28/08

CHECKED

ISSUED

SHEET

1 OF 1

**Amphenol Connex**

7/16 FEMALE TO FEMALE ADAPTER

272135

CAD FILE

C:/272/272135.DWG

DWG. NO.

272135.DWG

REV.

A

SIZE

A

SCALE

NA

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[272135](#)