



REV.	DATE	DESCRIPTION
NC	12/09/00	INITIAL RELEASE



DESCRIPTION	MATERIAL	FINISH	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS	APPROVALS	DATE	 Connex Connector Corporation			
1 CONT. SOCKET	BER. COPPER	GOLD	DIMENSIONS IN [] ARE IN INCHES FOR CUSTOMER REFERENCE ONLY UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5-6 = ± 0.2 6-30 = ± 0.4 30-120 = ± 0.6 120-315 = ± 1 315-1000 = ± 1.6 1000-2000 = ± 2.4	DRAWN G.R.S.	12/09/00				
2 BODY	BRASS	GOLD		CHECKED					
3 INSULATOR	TEFLON	NATURAL		ISSUED					
4 CONTACT PIN	BRASS	GOLD				TITLE SMB "T" ADAPTOR JACK-PLUG-JACK			
5						SIZE	FSCM NO.	DWG. NO.	REV.
6						A	99001	142300.DWG	NC
7									
8			DO NOT SCALE DRAWING			SCALE NA	PART NO. 142300	SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[142300](#)