

NOTES:

1. MATERIALS AND FINISHES:

TNC BULKHEAD JACK, IP 67 COMPLIANT - P/N: 122529-10  
 MICRO COAX PLUG TERMINATED USING 1.32 MM CABLE - P/N: 100910-01



2. ELECTRICAL:

A. IMPEDANCE: 50 OHM, NOMINAL

3. PACKAGING:

A. QUANTITY: SINGLE PACK  
 B. BAG TO BE MARKED: AMPHENOL RF, 336209-13-XXXX, AND DATE CODE

336209-13-XXXX		REVISIONS			
DRAWING NO.	REV	DESCRIPTION	DATE	ECO	APPR
THIRD ANGLE PROJ.	A	RELEASE TO MFG.	23-Sep-10	--	KR
	B	SEE SHEET 1	25-Oct-10	2113	KR
	C	SEE SHEET 1	05-Jul-11	2193	HR
	D	SEE SHEET 1	17-Jan-12	2270	CL
	F	SEE SHEET 1	27-Mar-14	2716	MB/BCG



ORDERING INFORMATION	
PART NUMBER (METRIC)	LENGTH IN INCHES * [METERS]
336209-13-0050	1.97 [0.050]
336209-13-0075	2.95 [0.075]
336209-13-0100	3.94 [0.100]
336209-13-0150	5.91 [0.150]
336209-13-0200	7.87 [0.200]
336209-13-0250	9.84 [0.250]
336209-13-0300	11.81 [0.300]

TOLERANCE TABLE	
LENGTH IN INCHES/FT [METERS]	TOLERANCE
0" - 23.90" [0 - 0.607]	±0.25" [0.006]
24.00" - 59.00" [0.610 - 1.499]	±0.50" [0.013]
5.0' - 24.9' [1.524 - 7.617]	±2.5%
25.0' & UP [7.620 & UP]	±5.0%

**DESIGN REQUIREMENTS:**

<input checked="" type="checkbox"/> FREQUENCY: DC TO 6.0 GHz	<input checked="" type="checkbox"/> CONTINUITY
<input type="checkbox"/> VSWR _____ : 1 MAX	<input checked="" type="checkbox"/> HI-POT :200 VRMS
<input type="checkbox"/> INS. LOSS _____ dB MAX	<input type="checkbox"/> OTHER

\* ADDITIONAL LENGTHS CAN BE PROVIDED, CONTACT AMPHENOL RF MARKETING FOR QUOTE

**CUSTOMER OUTLINE DRAWING**  
 ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, TOLERANCES ARE AS FOLLOWS: 2 PLACE DECIMAL ±.015 (0,381 mm)    3 PLACE DECIMAL ±.005 (0,127 mm)    ANGLES ± 1°	MATERIAL	DRAWN	DATE	TITLE TNC BULKHEAD JACK, IP 67 COMPLIANT TO MICRO COAX PLUG TERMINATED, USING 1.32 MM CABLE, VARIOUS LENGTHS	Amphenol Connex
	SEE NOTES	MOHAN	18-Mar-14		
NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol Corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights or permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.	REFERENCE	ENGINEER	DATE	SCALE: 4.0:1	SHEET 2 OF 2
		MOHAN	18-Mar-14		
		APPROVED	DATE		
		B.C. GLEISSNER	27-Mar-14		
		CAD FILE		DWG SIZE	DRAWING NO.
				B	336209-13-XXXX
					REV E

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[336209-13-0050](#) [336209-13-0100](#) [336209-13-0150](#) [336209-13-0200](#) [336209-13-0250](#) [336209-13-0300](#) [336209-13-0075](#)