




THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1650710	2016-04-16	Spring	Add ground pin



3	White	白
2	Green	緑
1	Black	黒
Conn.	Wire Color	
Pin Out		

CC-03AFMM-QR8EXX
XX: 01~99Meters
01: 01Meter
02: 02Meters
:
:
99: 99Meters

- Note:
- * $\varnothing$ Important Dimension To Check.
 - * Working Voltage Rating: 300V AC
 - * Working Current Rating: Max. 20A
 - * Waterproof Rate: IP68.(Mated) in 1 meter water within 24 hours
 - * Connector: Nylon+GF, Black.
 - * Pin: Copper Alloy, Glod & Ni Plated.
 - * Lock Nut: Nylon+GF, Black.
 - * Cable: SJTW 12WG*3C, Black, PVC Jacket, OD=11.7mm.
 - * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

Pin Assignments
Front View

UNIT:mm		TOLERANCE		TITLE		ITEM NO		DRAWN BY		DATE	
±0.5				X Lok C-Size 90° Cable 3 Pin 20A F Conn. M Pin		CC-03AFMM-QR8EXX		Spring		2016-04-16	
				SCALE 6:5		DWG NO		CHECKED BY		DATE	
				SIZE A4		CUSTOMER		Fisher		2016-04-16	
				SHEET 1 OF 1		ALTW		APPROVED BY		DATE	
				REV. B				Kevin		2016-04-16	
				WC-REV. A.3							
				$\varnothing$ Inspection item							

Amphenol LTW
安費諾亮泰企業股份有限公司

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CC-03AFMM-QR8E04](#) [CC-03AFMM-QR8E05](#) [CC-03AFMM-QR8E02](#) [CC-03AFMM-QR8E03](#) [CC-03AFMM-QR8E10](#)