




THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LE31680203	2016-07-18	Tom Gu	Change Part No. of Half Finished



3	White	白
2	Green	綠
1	Black	黑
Conn.	Wire Color	
Pin Out		

Conn.
BD-03AFFM-QR8EXX
XX : 01~99Meters
01 : 01Meter
02 : 02Meters
...
99 : 99Meters

Note:
* L Important Dimension To Check.
* Waterproof Rate: IP68 (Mated)
(in 1 meter water within 24 hours)
* Working Voltage Rating: AC 300 V
* Working Current Rating: 5A
* Housing: Nylon+GF, Black.
* Female Pin: Copper Alloy, Gold Plated.
* Rubber: Silicon, Gray
* Cable: SJTW 18AWG*3C + Filler
PVC Jacket UV Resistant, OD=8.0, Black.
* Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

UNIT:mm		TITLE
TOLERANCE	± 0.5	X-Lok B-Size (Power) Molding F Conn F 3 Pin
SCALE	6:5	SIZE A4
REV.	B	SHEET 1 OF 1
WC-REV.	A.1	QC: Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
DWG NO	Tom Gu	2016-07-18
CUSTOMER	CHECKED BY	DATE
ALTW	Spring Liu	2016-07-18
	APPROVED BY	DATE
	Kevin Hu	2016-07-18

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[BD-03AFFM-QR8E02](#) [BD-03AFFM-QR8E04](#) [BD-03AFFM-QR8E10](#) [BD-03AFFM-QR8E03](#) [BD-03AFFM-QR8E05](#)