




THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION



Pin Assignments
Front View

3	Red	紅
2	Brown	棕
1	Black	黑
Conn.	Wire Color	
Pin Out		

BD-03AFFM-QR8DXX

XX : 01~99Meters
01 : 01Meter
02 : 02Meters
:
99 : 99Meters

- Note:
- * QC Important Dimension To Check.
 - * Waterproof Rate: IP68(Mated)
 - * Working Voltage Rating: AC 300 V
 - * Working Current Rating: 5A
 - * Flame Class: UL94V-0 (UV Resistance)
 - * Housing: Nylon+GF, Black.
 - * Female Pin: Copper Alloy, Gold Plated.
 - * Rubber: Silicon, Gray
 - * Cable: UL21388 20AWG*3C+AL+My
PVC Jacket UV Resistant, OD=5.5, Black.
 - * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

UNIT:mm		TOLERANCE .X ±0.5		TITLE X-Lok B-Size Molding F Conn F 3 Pin		ITEM NO		DRAWN BY Micky		DATE 2014-10-20	
SCALE 6:5		SIZE A4		SHEET 1 OF 1		DWG NO BD-03AFFM-QR8DXX		CHECKED BY Spring		DATE 2014-10-20	
REV. A		WC-REV. A.1		<u>QC</u> : Inspection item		CUSTOMER ALTW		APPROVED BY Kevin		DATE 2014-10-20	
1		2		3		4		5		6	
7		8		FMW10702-01-02A1							

Amphenol LTW
安費諾亮泰企業股份有限公司

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[BD-03AFFM-QR8D04](#) [BD-03AFFM-QR8D02](#) [BD-03AFFM-QR8D03](#) [BD-03AFFM-QR8D05](#) [BD-03AFFM-QR8D10](#)