


Conn.



Pin Assignments Front View



3	Red	紅
2	Brown	棕
1	Black	黑
Conn.	Wire Color	
Pin Out		

BD-03AMFM-QL8DXX

```

XX : 01~99Meters
01 : 01Meter
02 : 02Meters
      :
      :
99 : 99Meters

```

Cable Length(L):01~99Meters

Note:

- *  Important Dimension To Check.
- * Waterproof Rate: IP68 (Mated)
- * Working Voltage Rating: AC 300 V
- * Working Current Rating: 5A
- * Flame Class: UL94V-0 (UV Resistance)
- * Housing: Nylon+GF, Black.
- * Female Pin: Copper Alloy, Gold Plated.
- * Cable: UL21388 20AWG*3C+AL+My
PVC Jacket UV Resistant, OD=5.5, Black.
- * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

UNIT: mm

TOLERANCE	
.X	± 0.25
.XX	± 0.1
.XXX	± 0.05
ANGLES	$\pm 1^{\circ}$

TITLE	X-Lok B-Size Molding M Conn F 3Pin
-------	---------------------------------------

SCALE 3:2	SIZE A4	SHEET 1 OF 1
REV. A	WC-REV. A.2	QC: Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO BD-03AFMF-QL8DXX	DRAWN BY Micky	DATE 2014-10-20
DWG NO BD-03AFMF-QL8DXX	CHECKED BY Spring	DATE 2014-10-20
CUSTOMER ALTW	APPROVED BY Kevin	DATE 2014-10-20

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[BD-03AMFM-QL8D03](#) [BD-03AMFM-QL8D05](#) [BD-03AMFM-QL8D04](#) [BD-03AMFM-QL8D02](#) [BD-03AMFM-QL8D10](#)