





THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A	Initial Release	2016-02-16	Wes	Change Rev.01 To Rev.A
B	LE31660478	2016-06-23	Wes	Change Part NO. of Half-finished



Pin Assignments
Front View



3	Green	綠
2	White	白
1	Black	黑
Conn.	Wire Color	
Pin Out		

DC-03AFFM-QR8E XX

XX :01~99Meters
01 :01Meter
02 :02Meters
...
99 :99Meters

Cable Length(L):01~99Meters

- Note:
- * $\varnothing$ Important Dimension To Check.
 - * Working Voltage Rating: AC 300V
 - * Working Current Rating: Max. 20A
 - * Waterproof Rate: IP68(Mated)
In 1 meters water within 24hours.
 - * Housing: Nylon+GF, Black(UV Resistance)
 - * Female Pin: Copper Alloy, Gold & Ni Plated
 - * Cable: SJTW 12AWG*3C, PVC Jacket,
OD=11.7, Black.
 - * Cable Length Tolerance:01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

UNIT:mm		TITLE	X-Lok D Size Cable Molding 3 Pin F Connector F Pin(20A)		
TOLERANCE	±0.5	SCALE	1:1	SIZE	A4
		REV.	B	WC-REV.	A.5
				$\varnothing$ Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
DWG NO	CHECKED BY	DATE
CUSTOMER	APPROVED BY	DATE
ALTW	Kevin Hu	2016-06-23

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[DC-03AFFM-QR8E03](#) [DC-03AFFM-QR8E05](#) [DC-03AFFM-QR8E02](#) [DC-03AFFM-QR8E10](#) [DC-03AFFM-QR8E04](#)