



THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1680619	2016-08-03	Wes Fan	Modify Wire Color.




CD-09AFFM-QL8W00
Color: Black

White Printing
白色印刷




Conn.



- Note:
- * $\varnothing$ Important Dimension To Check.
 - * Working Voltage Rating: AC 300 V
 - * Working Current Rating: 5A
 - * Flame Class: UL94V-0 (UV Resistance)
 - * Waterproof Rate: IP68(Mated).
 - * Housing: Nylon+GF, Black.
 - * Female Pin: Copper Alloy, Gold Plated
 - * Cable: UL21388 20AWG*9C+AL/PET Tape Black,PVC Jacket UV Resistant, OD=7.6
 - * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

CD-09AFFM-QL8DXX

XX :01~99Meters
01 :01Meter
02 :02Meters
...
99 :99Meters



Pin Assignments
Front View

9	Brown	棕
8	Green	綠
7	Orange	橙
6	Blue	藍
5	Purple	紫
4	Yellow	黃
3	Black	黑
2	Red	紅
1	Gray	灰
Conn.	Wire Color	
	Pin Out	

UNIT:mm		TOLERANCE		TITLE		ITEM NO		DRAWN BY		DATE	
± 0.5				X Lok C-Size Cable 9 Pin 5A F Conn. F Pin		CD-09AFFM-QL8DXX		Wes Fan		2016-08-03	
				SCALE 1:1		DWG NO		CHECKED BY		DATE	
				REV. B		CUSTOMER		Spring Liu		2016-08-03	
				WC-REV. A.1		ALTW		APPROVED BY		DATE	
				QC:Inspection item				Kevin Hu		2016-08-03	

Amphenol LTW
安費諾亮泰企業股份有限公司

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CD-09AFFM-QL8D04](#) [CD-09AFFM-QL8D10](#) [CD-09AFFM-QL8D05](#) [CD-09AFFM-QL8D02](#) [CD-09AFFM-QL8D03](#)