



REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LE31140022~227	2011/04/11	Vicky	Modify Note.
C	LEN1530093-099	2015/02/10	Ruru	Change Logo
D	LEN1681365~371	2016/08/05	Joyy	Modify The SR




HDB-26AFFM-SL7AXX

XX: 01~99Meter
01: 01 Meter
02: 02 Meter

99: 99Meters

Cable Length(L): 01~99Meters

Shell	Drain	地線		
13	Black/White	黑/白	26	Gray/Black 灰/黑
12	Light Green	淺綠	25	Green/Black 綠/黑
11	Purple	紫	24	Yellow/Black 黃/黑
10	Orange	橘	23	Pink/Red 粉紅/紅
9	Black	黑	22	Pink/Back 粉紅/黑
8	Red	紅	21	Orange/Black 橘/黑
7	Pink	粉紅	20	Red/Black 紅/黑
6	Gray	灰	19	Puple/White 紫/白
5	Yellow	黃	18	Blue/White 藍/白
4	Green	綠	17	Green/White 綠/白
3	White	白	16	Orange/White 橘/白
2	Blue	藍	15	Red/White 紅/白
1	Brown	棕	14	Brown/White 棕/白
Conn.	Wire Color		Conn.	Wire Color
Pin Out				

① HDB-26AFFM-SL7000 △B
Color: Black

△B Note:

- * Ⓞ Important Dimension.
- * Waterproof Rate: IP67
- * Housing: ABS, Black
- * Female Pin: Copper Alloy, Gold Plated.
- * Gasket: EPDM, Black
- * Screw: Steel, Nickel Plated.
- * Cable: UL2464 26AWG*26C+Drain+Al/My, PVC Jacket (UV Resistant), OD=8.0mm, Black.
- * Cable Length Tolerance: 01M: ±40mm
02M~05M: ±60mm
06M~10M: ±100mm
11M~30~: ±200mm
31M~99M: ±500mm

UNIT:mm	TITLE	SCALE	SIZE	SHEET	OF
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°	High Density D-SUB Cable Screw 26P F Conn F Pin	1:2	A4	1	1
		REV. D	WC-REV. A.2	QC: Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
	Joyy	2016-08-05
DWG NO	CHECKED BY	DATE
HDB-26AFFM-SL7AXX	Ma Fei	2016-08-05
CUSTOMER	APPROVED BY	DATE
ALTW	Jerry	2016-08-05

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[HDB-26AFFM-SL7A20](#) [HDB-26AFFM-SL7A06](#) [HDB-26AFFM-SL7A04](#)