


F
E
D
C
B
A



M SAP - XX B M M M - S R 8 X XX

SAP: A-Code Plastic Nut

03: 3Pin
04: 4Pin
05: 5Pin
06: 6Pin
08: 8Pin
10: 10Pin
12: 12Pin

B: Cable Without S/R (線端無網尾)

M: Male Connector (公座)

M: Male Pin (公Pin)

XX: 01~99Meters
01: 01Meter
02: 02Meters
:
99: 99Meters

A: PVC UL2517 Cable, Yellow (PVC黃色外被線材)
B: PUR UL20549 Cable, Black (PUR黑色外被線材)
D: PVC UL2517 Cable, Black (PVC黑色外被線材)

8: IP68/69K (防水等級68/69K)

R: Right (90° 線端)

S: Screw (螺紋式)

M: Molding Type (射出成型)

	12P	PVC	6.0	26	MSAP-12BMMM-SR8DXX
	10P				MSAP-10BMMM-SR8DXX
	8P		5.5	24	MSAP-08BMMM-SR8DXX
	6P		5.0		MSAP-06BMMM-SR8DXX
	5P		5.1	22	MSAP-05BMMM-SR8DXX
	4P		4.8		MSAP-04BMMM-SR8DXX
	3P		4.5		MSAP-03BMMM-SR8DXX
	12P	PUR	6.0	26	MSAP-12BMMM-SR8BXX
	10P				MSAP-10BMMM-SR8BXX
	8P		5.5	24	MSAP-08BMMM-SR8BXX
	6P		5.0		MSAP-06BMMM-SR8BXX
	5P		5.1	22	MSAP-05BMMM-SR8BXX
	4P		4.8		MSAP-04BMMM-SR8BXX
	3P		4.5		MSAP-03BMMM-SR8BXX
	12P	PVC	6.0	26	MSAP-12BMMM-SR8AXX
	10P				MSAP-10BMMM-SR8AXX
	8P		5.5	24	MSAP-08BMMM-SR8AXX
	6P		5.0		MSAP-06BMMM-SR8AXX
	5P		5.1	22	MSAP-05BMMM-SR8AXX
	4P		4.8		MSAP-04BMMM-SR8AXX
	3P		4.5		MSAP-03BMMM-SR8AXX
Contacts		Cable Jacket	Cable OD	AWG	Item No.



UNIT:mm				TITLE	
TOLERANCE		±0.5mm		M12 A Type 90° Male Conn.	
				SCALE	3:2
				SIZE	A4
REV.		C		SHEET	2 OF 3
WC-REV.		A.1		QC: Inspection item	


Amphenol LTW
安費諾亮泰企業股份有限公司


ITEM NO		DRAWN BY		DATE	
MSAP-XXBMMM-SR8XXX		Yulong_wang		2016-08-13	
		CHECKED BY		DATE	
		Jinhai		2016-08-13	
CUSTOMER		APPROVED BY		DATE	
ALTW		Jerry		2016-08-13	

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.




A triangle with the letter 'C' inside it.


[illegible]

Pin Out


3P




4P




5P




6 P



8P



10P



12P

Pin Assignments Front View

UNIT:mm		TITLE M12 A Type 90° Male Conn.			Amphenol LTW 安費諾亮泰企業股份有限公司	ITEM NO	DRAWN BY Yulong_wang	DATE 2016-08-13
TOLERANCE ±0.5mm		SCALE 3:2	SIZE A4	SHEET 3 OF 3		DWG NO MSAP-XXBMMM-SR8XXX	CHECKED BY Jinhai	DATE 2016-08-13
		REV. C	WC-REV. A.1	QC: Inspection item		CUSTOMER ALTW	APPROVED BY Jerry	DATE 2016-08-13

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

[MSAP-06BMMM-SR8B10](#) [MSAP-06BMMM-SR8D04](#) [MSAP-08BMMM-SR8B10](#) [MSAP-06BMMM-SR8B03](#) [MSAP-03BMMM-SR8A10](#) [MSAP-08BMMM-SR8D04](#) [MSAP-12BMMM-SR8B05](#) [MSAP-04BMMM-SR8D04](#) [MSAP-05BMMM-SR8D05](#) [MSAP-12BMMM-SR8B02](#) [MSAP-10BMMM-SR8B04](#) [MSAP-03BMMM-SR8A03](#) [MSAP-12BMMM-SR8A04](#) [MSAP-10BMMM-SR8D05](#) [MSAP-03BMMM-SR8D05](#) [MSAP-10BMMM-SR8D02](#) [MSAP-08BMMM-SR8D05](#) [MSAP-10BMMM-SR8D03](#) [MSAP-05BMMM-SR8A10](#) [MSAP-05BMMM-SR8D02](#) [MSAP-12BMMM-SR8D03](#) [MSAP-03BMMM-SR8B04](#) [MSAP-06BMMM-SR8A05](#) [MSAP-10BMMM-SR8D10](#) [MSAP-06BMMM-SR8A02](#) [MSAP-10BMMM-SR8B05](#) [MSAP-05BMMM-SR8B02](#) [MSAP-03BMMM-SR8B02](#) [MSAP-12BMMM-SR8A05](#) [MSAP-06BMMM-SR8A10](#) [MSAP-04BMMM-SR8B03](#) [MSAP-05BMMM-SR8B03](#) [MSAP-10BMMM-SR8B10](#) [MSAP-05BMMM-SR8B05](#) [MSAP-05BMMM-SR8D10](#) [MSAP-08BMMM-SR8D02](#) [MSAP-06BMMM-SR8B04](#) [MSAP-12BMMM-SR8B10](#) [MSAP-04BMMM-SR8A02](#) [MSAP-08BMMM-SR8B04](#) [MSAP-12BMMM-SR8A02](#) [MSAP-04BMMM-SR8A10](#) [MSAP-03BMMM-SR8B05](#) [MSAP-10BMMM-SR8B02](#) [MSAP-05BMMM-SR8A05](#) [MSAP-06BMMM-SR8A03](#) [MSAP-05BMMM-SR8A04](#) [MSAP-03BMMM-SR8D03](#) [MSAP-08BMMM-SR8A10](#) [MSAP-04BMMM-SR8B04](#) [MSAP-06BMMM-SR8D05](#) [MSAP-08BMMM-SR8B03](#) [MSAP-10BMMM-SR8A03](#) [MSAP-04BMMM-SR8A03](#) [MSAP-10BMMM-SR8A05](#) [MSAP-08BMMM-SR8A05](#) [MSAP-04BMMM-SR8D10](#) [MSAP-03BMMM-SR8D02](#) [MSAP-04BMMM-SR8B02](#) [MSAP-05BMMM-SR8A02](#) [MSAP-03BMMM-SR8B10](#) [MSAP-08BMMM-SR8A03](#) [MSAP-10BMMM-SR8A04](#) [MSAP-04BMMM-SR8A05](#) [MSAP-12BMMM-SR8D10](#) [MSAP-06BMMM-SR8A04](#) [MSAP-03BMMM-SR8A02](#) [MSAP-08BMMM-SR8B02](#) [MSAP-06BMMM-SR8D02](#) [MSAP-08BMMM-SR8A02](#) [MSAP-12BMMM-SR8D02](#) [MSAP-12BMMM-SR8A03](#) [MSAP-08BMMM-SR8A04](#) [MSAP-10BMMM-SR8D04](#) [MSAP-04BMMM-SR8A04](#) [MSAP-12BMMM-SR8A10](#) [MSAP-10BMMM-SR8A02](#) [MSAP-10BMMM-SR8B03](#) [MSAP-03BMMM-SR8B03](#) [MSAP-03BMMM-SR8D04](#) [MSAP-04BMMM-SR8D03](#) [MSAP-12BMMM-SR8B04](#) [MSAP-05BMMM-SR8B10](#) [MSAP-05BMMM-SR8D04](#) [MSAP-06BMMM-SR8B02](#) [MSAP-12BMMM-SR8B03](#) [MSAP-12BMMM-SR8D05](#) [MSAP-10BMMM-SR8A10](#) [MSAP-05BMMM-SR8B04](#) [MSAP-04BMMM-SR8D05](#) [MSAP-03BMMM-SR8A04](#) [MSAP-08BMMM-SR8B05](#) [MSAP-04BMMM-SR8B05](#) [MSAP-04BMMM-SR8B10](#) [MSAP-05BMMM-SR8A03](#) [MSAP-06BMMM-SR8B05](#) [MSAP-12BMMM-SR8D04](#) [MSAP-03BMMM-SR8D10](#) [MSAP-05BMMM-SR8D03](#) [MSAP-06BMMM-SR8D10](#)