



THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1440194	2014/05/10	Tom	Upated The Note
C	LEN1490328	21014/09/06	Joyy	Change to 94V0 material



Drain Wire	接地	Shield
Brown	棕	8
White/Brown	白/棕	7
Green	綠	6
White/Blue	白/藍	5
Blue	藍	4
White/Green	白/綠	3
Orange	橘	2
White/Orange	白/橘	1
Wire Color		Plug
Pin Out		



XX: 01~99Meter
01: 01Meter
02: 02Meters
:
:
99: 99Meters
Cable Length(L):01~99Meters

Note:
* Important Dimention To Check.
* Waterproof Rate:IP67
* Plug: PC, Gold Plated
* Screw Nut: Nylon+GF, Black
* Gasket: Silicone, Gray
* Cable: CAT5E FTP, OD:Ø6.5mm, Black
* Cable Length Tolerance: 01M:±40mm
02~05M:±60mm
06~10M:±100mm
11~30M:±200mm
30~99M:±500mm

UNIT:mm		TITLE
TOLERANCE	±0.5	RJ D SIZE RIGHT ANGEL CABLE
SCALE	1:1	SIZE A4
REV.	C	WC-REV. A.11
		QC:Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
DWG NO	Joyy	2014-09-06
RDP-5SAMMM-SRM7BXX	CHECKED BY	DATE
CUSTOMER	Tom	2014-09-06
ALTW	APPROVED BY	DATE
	Victor	2014-09-06

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[RDP-5SAMMM-SRM7B02](#)