



THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1540298	2015-04-16	Micky	Modify #2 Wire Colore



Pin Assignments
Front View




2	Red	紅
1	Black	黑
Conn.	Wire Color	
Pin Out		



BB-02AFFM-QR8DXX

XX : 01~99Meters
01 : 01Meter
02 : 02Meters
... : ...
99 : 99Meters

Note:
* $\varnothing$ Important Dimension To Check.
* Waterproof Rate: IP68(Mated, 1M/24H)
* Working Voltage Rating: AC 300 V
* Working Current Rating: 10A
* Flame Class: UL94V-0
* Housing: Nylon+GF, Black.(UV Resistance)
* Female Pin: Copper Alloy, Gold Plated.
* Rubber: Silicon, Gray
* Cable: UL21388 16AWG*2C+AL+My
PVC Jacket UV Resistant, OD=6.0, Black.
* Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm



UNIT:mm		TOLERANCE .X ±0.5		TITLE X-Lok B-Size Molding F Conn F 2 Pin		ITEM NO		DRAWN BY Micky		DATE 2015-04-16	
SCALE 6:5		SIZE A4		SHEET 1 OF 1		DWG NO BB-02AFFM-QR8DXX		CHECKED BY Spring		DATE 2015-04-16	
REV. B		WC-REV. A.2		QC: Inspection item		CUSTOMER ALTW		APPROVED BY Kevin		DATE 2015-04-16	

Amphenol LTW
安費諾亮泰企業股份有限公司

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[BB-02AFFM-QR8D04](#) [BB-02AFFM-QR8D02](#) [BB-02AFFM-QR8D05](#) [BB-02AFFM-QR8D03](#)