




THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION



8A-03AMMM-SL7AXX
XX: 01~99Meters
01: 01Meter
02: 02Meter
...
99: 99Meters
Cable Length(L): 01~99Meters

- Note:
- * (CC) Important Dimension.
 - * Waterproof Rate: IP67.
 - * Connector: PU, Black.
 - * Male Pin: Copper Alloy, Gold Plated.
 - * Screw Nut: Zinc Alloy, Nickel Plated.
 - * Cable: UL2464 22AWG*3C+Talcum, PVC Jacket, UV Resistant, OD=5.0, Black.
 - * Cable Length Tolerance: 01M: ±40mm
02~05M: ±60mm
06~10M: ±100mm
11~30M: ±200mm
31~99M: ±500mm



Pin Assignments
Front View

4	Black 黑
3	Blue 藍
1	Brown 棕
Conn.	Wire Color
Pin Out	

UNIT:mm		TITLE
TOLERANCE	±0.5 mm	M8 3Pin Cable M Conn. M Pin
SCALE	2:1	SIZE A4
REV.	A	SHEET 1 OF 1
WC-REV.	A.4	(CC): Inspection item

Amphenol LTW		ITEM NO	DRAWN BY	DATE
安費諾亮泰企業股份有限公司		DWG NO	Mila	2014-01-09
		CUSTOMER	Jimmy	2014-01-09
		APPROVED BY	Jerry	2014-01-09

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[8A-03AMMM-SL7A04](#)