




THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

1	2	3	4	5	6	7	8
REV.	ECN NO.	DATE	SIGN	DESCRIPTION			



Pin Assignments
Front View

4	Orange	橙
3	Red	紅
2	Brown	棕
1	Black	黑
Conn.	Wire Color	
Pin Out		

CB-04AMMM-QL8DXX

XX :01~99Meters
01 :01Meter
02 :02Meters
:
:
99 :99Meters

- Note:
- * $\varnothing$ Important Dimension To Check.
 - * Working Voltage Rating: AC 300 V
 - * Working Current Rating: 10A
 - * Flame Class: UL94V-0 (UV Resistance)
 - * Waterproof Rate: IP68(Mated).
 - * Housing: Nylon+GF, Black.
 - * Male Pin: Copper Alloy, Gold Plated
 - * Cable: UL21388 16AWG*4C+AL.Mylar Black,PVC Jacket UV Resistant, OD=6.8
 - * Cable Length Tolerance:01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

A	UNIT:mm		TOLERANCE ±0.5		TITLE X Lok C-Size Cable 4Pin 10A M Conn. M Pin			ITEM NO		DRAWN BY Micky		DATE 2014-11-18	
	SCALE 3:2		SIZE A4		SHEET 1 OF 1			DWG NO CB-04AMMM-QL8DXX		CHECKED BY Spring		DATE 2014-11-18	
	REV. A		WC-REV. A.2		$\varnothing$ Inspection item			CUSTOMER ALTW		APPROVED BY Kevin		DATE 2014-11-18	
												8 FMW10702-01-02A1	

Amphenol LTW
安費諾亮泰企業股份有限公司

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CB-04AMMM-QL8D10](#) [CB-04AMMM-QL8D03](#) [CB-04AMMM-QL8D04](#) [CB-04AMMM-QL8D15](#) [CB-04AMMM-QL8D05](#)
[CB-04AMMM-QL8D02](#) [CB-04AMMM-QL8D20](#)