



THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1450014	2014-04-28	Tom_gu	Change D Cut




Cable Length(L): 100~1000mm

RDP-5SPFFP-SCM7BXX

XX:	100~1000mm
10:	100mm
15:	150mm
20:	200mm
95:	950mm
A0:	1000mm

Cable length	Tolerance
0.0~100 mm	±10 mm
101~300 mm	±15 mm
301~1000 mm	±20 mm

- Note:
- * $\varnothing$ Important Dimension
 - * Waterproof Rate : IP67,MATED WATERPROOF
 - * Housing : Nylon+GF,BLACK
 - * Screw Nut : Nylon+GF,BLACK
 - * Gasket : Silicone,UL 94V-0,Gray.
 - * PCB: FR-4
 - * Cable: CAT5E FTP 24#*4P+D+AL/MY,6.5
 - * Jack : PBT Polyester UL 94V-0
 - * Panel Thickness Max: 3.0mm
 - * Screw torsion value range: 8~15kgf-cm




Recommended Panel Cut-out Rear View

Shield	Drain Wire	接地線	Shield
8	Brown	棕	8
7	White/Brown	白/棕	7
6	Green	綠	6
5	White/Blue	白/藍	5
4	Blue	藍	4
3	White/Green	白/綠	3
2	Orange	橘	2
1	White/Orange	白/橘	1
Jack	Wire Color	Plug	
Pin Out			

Twist

Twist

Twist



UNIT : mm		TITLE		ITEM NO		DRAWN BY		DATE	
TOLERANCE		RJ45,D SIZE,MATED WATERPROOF		RDP-5SPFFP-SCM7BXX		Tom_gu		2014-04-28	
SCALE		SIZE		CUSTOMER		CHECKED BY		DATE	
1:1		A4		ALTW		Tony		2014-04-28	
REV.		WC-REV.		APPROVED BY		Victor		DATE	
B		A.5		Inspection item				2014-04-28	

Amphenol LTW

安費諾亮泰企業股份有限公司

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[RDP-5SPFFP-SCM7B20](#) [RDP-5SPFFP-SCM7BA0](#) [RDP-5SPFFP-SCM7B15](#)