



Pin Assignments

Front View

4	Orange	橙
3	Red	紅
2	Brown	棕
1	Black	黑
Conn.	Wire Color	
	Pin Out	

CB-04AMFM-QL8DXX

```

XX : 01~99Meters
01 : 01Meter
02 : 02Meters
:
:
99 : 99Meters

```

- *  Important Dimension To Check.
- * Working Voltage Rating: AC 300 V
- * Working Current Rating: 10A
- * Flame Class: UL94V-0 (UV Resistance)
- * Waterproof Rate: IP68(Mated).
- * Housing: Nylon+GF, Black.
- * Female Pin: Copper Alloy, Gold Plated
- * Cable: UL21388 16AWG*4C+AL.Mylar
Black,PVC Jacket UV Resistant, OD=6.8
- * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

UNIT : mm		
TOLERANCE		
± 0.5		

TITLE	X Lok C-Size Cable 4Pin 10A M Conn. F Pin
-------	--

SCALE 3:2	SIZE A4	SHEET 1 OF 1
REV. A	WC-REV. A.3	QC: Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
	Micky	2014-11-18
DWG NO	CHECKED BY	DATE
CB-04AMFM-QL8DXX	Spring	2014-11-18
CUSTOMER	APPROVED BY	DATE
ALTW	Kevin	2014-11-18

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CB-04AMFM-QL8D05](#) [CB-04AMFM-QL8D02](#) [CB-04AMFM-QL8D03](#) [CB-04AMFM-QL8D10](#) [CB-04AMFM-QL8D04](#)