





THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION



Pin Assignments
Front View

6	Green 綠
5	Yellow 黃
4	Orange 橘
3	Red 紅
2	Brown 棕
1	Black 黑
Conn.	Wire Color

8A-06AFFM-SR7AXX
XX: 01~99Meters
01: 01Meter
02: 02Meter
:
:
99: 99Meters
Cable Length(L): 01~99Meters

- Note:
- * (QC) Important Dimension.
 - * Waterproof Rate: IP67.
 - * Connector: PU, Black.
 - * Female Pin: Copper Alloy, Gold Plated.
 - * Screw Nut: Zinc Alloy, Nickel Plated.
 - * O-Ring: Viton, Green.
 - * Cable: UL2464 24AWG*6C+Al/Mylar, PVC Jacket, UV Resistant, OD=5.0, Black.
 - * Cable Length Tolerance: 01M: ±40mm
02~05M: ±60mm
06~10M: ±100mm
11~30M: ±200mm
31~99M: ±500mm

UNIT:mm		TOLERANCE ±0.5 mm		TITLE M8 6Pin Cable F Conn. F Pin		ITEM NO		DRAWN BY Mila		DATE 2014-01-09	
SCALE 2:1		SIZE A4		SHEET 1 OF 1		DWG NO 8A-06AFFM-SR7AXX		CHECKED BY Jimmy		DATE 2014-01-09	
REV. A		WC-REV. A.2		(QC): Inspection item		CUSTOMER ALTW		APPROVED BY Jerry		DATE 2014-01-09	

Amphenol LTW
安費諾亮泰企業股份有限公司

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[8A-06AFFM-SR7A04](#)