



THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.


REV.	ECN NO.	DATE	SIGN	DESCRIPTION
E	LE31350198~201	2013/05/24	Yulong	Add the Ball Mark
F	LENI380078~81	2013/07/27	Yulong	Update the Drawing
G	LENI490390~393	2014/09/09	Sam	Change Logo



Shell	Braid	纏繞	
19	Pink	粉紅	3
18	Purple	紫	3
17	Red	紅	3
16	Orange	橘	2
15	Yellow	黃	
14	Gray	灰	3
13	White	白	3
12	White	白	
11	Drain	地線	1
10	Blue	藍	
9	White	白	
8	Drain	地線	1
7	Green	綠	
6	White	白	
5	Drain	地線	1
4	Red	紅	
3	White	白	
2	Drain	地線	1
1	Brown	棕	

Type 3	IC
Type 2	IP

Conn.	Wire Color	Wire Type	Type 1	IP+D+AL
Pin Out		Wire Type		



Amphenol LTW
安費諾亮泰企業股份有限公司

- Note:
- * (C) Important Dimension.
 - * Waterproof Rate: IP67
 - * Plug: HDMI 19 Pins Male
 - * Cable: (26#*1P+D+AL+MYLAR)*4+26#*1P+26#*5C +AL+B UL20276, Black, OD=8.5mm.
 - * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm

XX : 01~05Meters
01 : 01Meter
02 : 02Meters
:
:
05 : 05Meters
Cable Length(L): 01~05Meters

UNIT:mm		TITLE	HDMI Cable Latch 19 M Conn M Pin	
TOLERANCE ±0.5		SCALE	1:1	SIZE A4
		REV.	G	WC-REV. B.2
		SHEET 1 OF 1		
		QC: Inspection item		

ITEM NO	DRAWN BY	DATE
DWG NO	Sam	2014-09-19
CUSTOMER	Vicky	2014-09-19
ALTW	Rita	2014-09-19

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[HP-19AMMM-QL7A04](#)