



REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1670234	2016/07/18	Feng_Li	Add Cable Length Tolerance



ROP-5SAMMM-TLM7000 1

ROP-5SAMMM-TLM7BXX

XX: 01~99Meter
01: 01Meter
02: 02Meters
:
99: 99Meters

Cable Length(L):01~99Meters

Note:

- * Waterproof Rate: IP67.
- * Housing: Nylon, Black.
- * Plug: PC, Gold Plated, Shielded
- * Lock Nut: Nylon+GF, Black.
- * Gasket: Silicone, Black.
- * Seal: Silicone, Black.
- * Sealing Nut: Nylon, Black.
- * Cable: FTP, 24#*4P+MY+D+AL/MY, OD6, Black.
- * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

Drain Wire	接地	Shield
Brown	棕	8
White/Brown	白/棕	7
Green	綠	6
White/Blue	白/藍	5
Blue	藍	4
White/Green	白/綠	3
Orange	橘	2
White/Orange	白/橘	1
Wire Color		Plug
Pin Out		

Twist
對絞Twist
對絞Twist
對絞Twist
對絞

UNIT:mm	
TOLERANCE	
.X	±0.25
.XX	±0.1
.XXX	±0.05
ANGLES	±1°

TITLE	RJ45 Plug Cable, ODVA, Cat 5e		
SCALE	1:1	SIZE	A4
REV.	B	WC-REV.	A.9
		SHEET	1 OF 1
		QC	Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
DWG NO	Feng_Li	2016-07-18
CUSTOMER	CHECKED BY	DATE
ALTW	Jinhai	2016-07-18
	APPROVED BY	DATE
	Jerry	2016-07-18

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[ROP-5SAMMM-TLM7B02](#)